Engineering Specification

| Job Name | Contractor |
|--------------|-----------------------|
| Job Location | Approval |
| JOD LOCATION | Approvai |
| Engineer | Contractor's P.O. No. |
| ŭ | |
| Approval | Representative |

Dead Level® Z

Flanged Deck Channel


Specification


Watts Dead Level® Z deck channel system with 6" wide x 48" long (standard) ductile iron frame, UV stabilized talc-filled polypropylene channels with integral 4" IPS threaded bottom outlet. System will be frame-anchored, with (specify) grating to suit DIN Class (specify) load rating. System to include frame anchors, grate lock-downs, and construction covers. System can be specified in 12" increments. Installation to be performed in accordance with manufacturer's installation instructions.


Call customer service if you need assistance with technical details.

| Options | | | |
|---------|------------------------------|--|--|
| Suffix | Description | | |
| -FG | Galvanized Steel Frame Guard | | |
| -FS | Stainless Steel Frame Guard | | |

| Grate Options | | | |
|---------------|---------------------------------------|-----------|--|
| Suffix | Description | Class | |
| -DI | Ductile Iron | Class F □ | |
| -DI-ADA | Ductile Iron ADA | Class F 🗆 | |
| GDI | Galvanized Ductile Iron* | Class F 🗆 | |
| -RGP | Reinforced Galvanized Perforated | Class E 🗆 | |
| -RGS | Reinforced Galvanized Slotted | Class E 🗆 | |
| -RSP | Reinforced Stainless Steel Perforated | Class E 🗆 | |
| -RSS | Reinforced Stainless Steel Slotted | Class E 🗆 | |







NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.

WATTS®

USA: T: (800) 338-2581 • Watts.com **Canada:** T: (888) 208-8927 • Watts.ca

Latin America: T: (52) 55-4122-0138 • Watts.com

ES-WD-DeadLevel-Z 2504 © 2025 Watts