

Engineering Specification

Job Name _____
 Job Location _____
 Engineer _____
 Approval _____
 Tag _____

Contractor _____
 Approval _____
 Contractor's P.O. No. _____
 Representative _____


RD-200 Small Area Roof Drain Specification

Watts RD-200 epoxy coated cast iron roof drain with flashing clamp with integral gravel stop, self-locking polyethylene dome (standard), and no hub (standard) outlet.

| Pipe Sizing | |
|-------------|------------------------------------------------------|
| Suffix | Description |
| 2 | 2"(51) Pipe Size <input type="checkbox"/> |
| 3 | 3"(76) Pipe Size <input type="checkbox"/> |
| 4 | 4"(102) Pipe Size (NH Only) <input type="checkbox"/> |

| Outlet Type | |
|-------------|---------------------------------------|
| Suffix | Description |
| NH | No Hub (MJ) <input type="checkbox"/> |
| P | Push On <input type="checkbox"/> |
| T | Threaded <input type="checkbox"/> |
| X | Inside Caulk <input type="checkbox"/> |

| Options | |
|---------|-----------------------------------------------------------|
| Suffix | Description |
| -13 | Galvanized Body & Flashing Clamp <input type="checkbox"/> |
| -B | Sump Receiver <input type="checkbox"/> |
| -D | Underdeck Clamp <input type="checkbox"/> |
| -F | Deck Flange/Adj. Extension <input type="checkbox"/> |
| -GSS | Stainless Steel Ballast Guard <input type="checkbox"/> |
| -K | Ductile Iron Dome <input type="checkbox"/> |
| -K13 | Galvanized Dome <input type="checkbox"/> |
| -K80 | Aluminum Dome <input type="checkbox"/> |
| -K81 | Rough Bronze Dome <input type="checkbox"/> |
| -K83 | SS Mesh Covered Dome <input type="checkbox"/> |
| -L | Vandal Proof Dome <input type="checkbox"/> |
| -R | 2" External Water Dam <input type="checkbox"/> |
| -SO | Side Outlet <input type="checkbox"/> |
| -W | Adjustable Internal Water Dam <input type="checkbox"/> |



| Pipe Size | Std. No Hub | P Push On | T Female Thread | X Inside Caulk | 60/61 PVC/ABS |
|-----------|-------------|-------------|-----------------|----------------|---------------|
| 2"(51) | 3 5/8"(92) | 4 1/4"(108) | 4 1/4"(108) | 4 1/2"(108) | 4"(102) |
| 3"(76) | 3 5/8"(92) | 4 1/4"(108) | 4 1/4"(108) | 4 1/2"(108) | 4"(102) |
| 4"(102) | 3 5/8"(92) | 4 1/4"(108) | 4 1/4"(108) | 4 1/2"(108) | 4"(102) |

Deck Opening 6 1/2"(165)
with Sump Receiver 8"(203)

NOTICE
 The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

| Optional Body Material | |
|------------------------|---------------------------------------------------|
| Suffix | Description |
| -60 | PVC Body w/Socket Outlet <input type="checkbox"/> |
| -61 | ABS Body w/Socket Outlet <input type="checkbox"/> |

Free Area
Sq. In.
35

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



USA: T: (800) 338-2581 • F: (828) 248-3929 • Watts.com
 Canada: T: (888) 208-8927 • F: (905) 481-2316 • Watts.ca
 Latin America: T: (52) 55-4122-0138 • Watts.com