Engineering Specification

Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No.
Approval	Rep Agency & Sales Agent

RainCycle™ RCS-7600

Rainwater System Package -Direct Pumping, Below Grade Cistern, Submersible Pump

Overview

RainCycle™ RCS-7000 Series packages are stand-alone building scale systems for collecting, storing, filtering, and treating roof-collected rainwater for non-potable end uses. This series integrates all the rainwater system functions in a single package.

Specification

The **7600 Series** captures, stores, filters, treats, and distributes roof-collected rainwater. Rainwater flowing from a clean roof surface is routed to an inlet pre-filter and then to a below grade cistern. The pre-filter mitigates the intrusion of larger coarser material such as leaves and twigs. A submersible pump, located in the cistern, boosts rainwater through the filtration skid to the end use. There are two options for providing a secondary water supply for the end uses in the event of low water levels in the cistern. The default option employs a factory installed automatic bypass valve located on the filtration skid that when opened, allows domestic water to flow directly to the end use. The second option is a field-installed motorized makeup valve that allows domestic water to flow into the cistern.

Exclusive Features

- A proprietary control algorithm allows the booster pumps to function without a hydropneumatic tank.
- Field adjustable pipe break detection technology is included in the controller to shutdown pumps during unusually high flow conditions which are indicative of a pipe break.
- Factory changes require rolling passwords. This allows only authorized users to make factory setting changes.

Other System Features:

- Filtration Rates up to 80 GPM
- 304 Stainless Steel Headers, Branch Piping and Frame
- 2-stage Cartridge-Type, Low Maintenance Filtration in a Non-Metallic Filter Body
- Fully Controlled, Auto-Dim UV
- Filtration Differential Pressure Monitoring
- Tank Level Monitoring
- UL 508a Control Panel with PLC and 7" Color Touch Screen
- All Alarms with Audio/Visual Display, Time-Delayed Proof of Condition, Auto-Reset and Control Logging
- RS485, Modbus/BACNet/LonWorks/OPC-UA (native)
 Communication



Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.





Filtration Skid

Roofing Surface Material

Description	Check One
Asphalt Shingle	
Metal	
Membrane Type	
Green Roof	
Other (Describe)	

Pre-Filter

Suffix	Description	Check One
FBO	Pre-filter (by others)	
FIB	Inside Building	
FOV	Outside Building in Vault	
FOB	Outside Building Direct Bury	
		Diameter/Area
	Inlet Pipe size to Pre-Filter	
	Roof Collection Area	

Cistern (Tank)

Suffix	Description	Check One
СВО	Cistern (by others)	
CAG	Above Grade	
CBG	Below Grade	
		Volume
	Tank Volume (gallons)	

Filtration Flow Rate

Suffix		Description	Check One
010	10 GPM		
015	15 GPM		
025	25 GPM		
040	40 GPM		
080	80 GPM		



System Voltage

Suffix	Description	Check One
115	115V/1ph/60hz Supply Power	
208	208V or 230V/3ph/60hz Supply Power	
460	460V/3ph/60hz Supply Power	
575	575V/3ph/60hz Supply Power	

Communication

Suffix	Description	Check One
NC	None	
MB	Modbus RTU (RS-485)	
BN	BACnet IP or MSTP	
CU	OPC-UA	

Booster Pump

Suffix	Description	Check One
BPO	Booster Pump (by others)	
BPW	Include Booster Pump Skid	
	Elevation Height from Booster Pump Outlet to Highest Fixture in Building (In Feet)	

End Use & Fixture Count



NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

WARNING

Rainwater supplied by Watts rainwater systems is non-potable water and is not intended for potable water applications. DO NOT DRINK WATER supplied from Watts rainwater systems and related equipment. Users shall determine the suitability of the product for the intended application before using.