

## Engineering Specification

Job Name \_\_\_\_\_

Contractor \_\_\_\_\_

Job Location \_\_\_\_\_

Approval \_\_\_\_\_

Engineer \_\_\_\_\_

Contractor's P.O. No. \_\_\_\_\_

Approval \_\_\_\_\_

Representative \_\_\_\_\_

# HY-725

## Non-Freeze Wall Hydrant with NB Box & Integral Vacuum Breaker

### Specification



Watts HY-725 concealed non-freeze key operated wall hydrant with nickel bronze box and door, chrome plated hydrant face, integral vacuum breaker, 3/4" hose connection, 3/4" female x 1" male pipe connection, all bronze head, seat casting and internal working parts, bronze wall casing, and loose key. Complies with ASME B1.20.7 and ASSE 1019-2004. UPC/IAPMO listed. Maximum operating pressure 125 psi.

Call customer service if you need assistance with technical details.

Wall Thickness	
Suffix	Description
-6	6"(152) Thick
-8	8"(203) Thick
-10	10"(254) Thick
-12	12"(305) Thick
-14	14"(356) Thick
-16	16"(406) Thick
-18	18"(457) Thick
-20	20"(508) Thick
-22	22"(559) Thick
-24	24"(610) Thick
Other	Specify _____

Options	
Suffix	Description
-K	Cylinder Lock
-88	Wall Clamp
-3	Stainless Steel Box
-CIA	Complete Internal Assembly (Repair Kit)
-R	Round Stainless Steel Box

**Recommended Wall Opening:**  
5 1/4"(133) x 6 1/4"(158)



Top View

### NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



USA: T: (800) 338-2581 • Watts.com

Canada: T: (888) 208-8927 • Watts.ca

Latin America: T: (52) 55-4122-0138 • Watts.com