

Engineering Specification

Job Name _____

Contractor _____

Job Location _____

Approval _____

Engineer _____

Contractor's P.O. No. _____

Approval _____

Representative _____

HY-420

Non-Freeze Wall Hydrant with Chrome Face & Integral Vacuum Breaker

Specification


Watts HY-420 non-freeze key operated wall hydrant with chrome plated face, integral vacuum breaker, 3/4" hose connection, 3/4" female x 1" male pipe connection, all bronze head, seat casting and internal working parts, bronze wall casing, and loose key. Complies with ASME B1.20.7, and ASSE 1019-2004, UPC/IAPMO listed. Maximum operating pressure 125 psi.

Call customer service if you need assistance with technical details.

Wall Thickness	
Suffix	Description
4	4"(102) Thick
6	6"(152) Thick
8	8"(203) Thick
10	10"(254) Thick
12	12"(305) Thick
14	14"(356) Thick
16	16"(406) Thick
18	18"(457) Thick
20	20"(508) Thick
22	22"(559) Thick
24	24"(610) Thick
Other	Specify _____

Options	
Suffix	Description
-88	Wall Clamp
-CIA	Complete Internal Assembly (Repair Kit)

Recommended Wall Opening:
2"(51) x 4"(102)



NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



USA: T: (800) 338-2581 • Watts.com

Canada: T: (888) 208-8927 • Watts.ca

Latin America: T: (52) 55-4122-0138 • Watts.com

ES-WD-HY-420 2518

© 2025 Watts

