For Commercial Applications

| Job Name | Contractor |
|--------------|-----------------------|
| Job Location | Approval |
| Engineer | Contractor's P.O. No. |
| Approval | Representative |
| Engineer | Contractor's P.O. No. |

Dead Level® S

Deck Channel with Ductile Iron Frame

Specification


Watts Dead Level® S deck channel system with 6"(152) wide x 48"(1219) long (standard) ductile iron frame, UV stabilized talc-filled polypropylene channels with integral 4"(102) IPS threaded bottom outlet. System shall be frame-anchored, with (specify) grating to suit DIN Class (specify) load rating. System to include frame connectors, grate lockdowns, and construction covers. System can be specified in 1'(305) increments. Installation to be performed in accordance with manufacturer's installation instructions.

| Grate Options | | | |
|---------------|---------------------------------------|----------|-----|
| Suffix | Description | Load Cla | ass |
| -BR | Decorative Bronze | Class B | |
| -DI | Ductile Iron | Class F | |
| -DI-ADA | Ductile Iron ADA | Class F | |
| -GDI | Galvanized Ductile Iron | Class F | |
| -GP | Galvanized Perforated | Class A | |
| -GS | Galvanized Slotted | Class A | |
| -PP | Polypropylene | Class A | |
| -RGP | Reinforced Galvanized Perforated | Class E | |
| -RGS | Reinforced Galvanized Slotted | Class E | |
| -RSP | Reinforced Stainless Steel Perforated | Class E | |
| -RSS | Reinforced Stainless Steel Slotted | Class E | |
| -SP | Stainless Steel Perforated | Class A | |
| -SS | Stainless Steel Slotted | Class A | |
| -SCI | Solid Cast Iron | Class F | |


| Suffix | Options Description | |
|--------|------------------------------|--|
| -FG | Galvanized Steel Frame Guard | |
| -FS | Stainless Steel Frame Guard | |

Please refer to watts.com for BAA information on specific models.





Typical Installation



NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.

