

Engineering Specification

Job Name \_\_\_\_\_

Job Location \_\_\_\_\_

Engineer \_\_\_\_\_

Approval \_\_\_\_\_

Contractor \_\_\_\_\_

Approval \_\_\_\_\_

Contractor's P.O. No. \_\_\_\_\_

Representative \_\_\_\_\_

FD-920

Parking Deck Drain

for Precast Slabs

Specification

Watts FD-920 epoxy coated cast iron parking deck drain with integral countersunk deck flange, 10 7/16" round top with secured ductile iron heel proof grate, gasket seal between body and top assembly, an no hub (standard) outlet.



Call customer service if you need assistance with technical details.

| PIPE SIZING |                   |
|-------------|-------------------|
| SUFFIX      | DESCRIPTION       |
| 2           | 2"(51) Pipe Size  |
| 3           | 3"(76) Pipe Size  |
| 4           | 4"(102) Pipe Size |
| 5           | 5"(127) Pipe Size |
| 6           | 6"(152) Pipe Size |
| 8           | 8"(203) Pipe Size |

| OUTLET TYPE |                 |
|-------------|-----------------|
| SUFFIX      | DESCRIPTION     |
| NH          | No Hub          |
| P           | Push On         |
| T           | Threaded Outlet |
| X           | Inside Caulk    |

| OPTIONS |                                                       |
|---------|-------------------------------------------------------|
| SUFFIX  | DESCRIPTION                                           |
| -5      | Sediment Bucket                                       |
| -6      | Vandal Proof                                          |
| -13     | All Galvanized                                        |
| -D      | Underdeck Clamp                                       |
| -SB     | Shallow Body 2 3/4" Deep<br>(3", 4", 6", NH/P, 8" NH) |

| LOAD RATING | FREE AREA SQ. IN. |
|-------------|-------------------|
| *XHD        | 29                |



NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.

