

Engineering Specification

Job Name _____	Contractor _____
Job Location _____	Approval _____
Engineer _____	Contractor's P.O. No. _____
Approval _____	Representative _____

HY-800 Non-Freeze Yard Hydrant


Specification

Watts HY-800 non-freeze yard hydrant with epoxy coated cast iron head with lift handle and lock option, galvanized casing, bronze internal working parts and valve housing, and 1/8" NPT drain port.



Call customer service if you need assistance with technical details.

Depth of Bury	
Suffix	Description
-1	1'(305) Depth
-2	2'(610) Depth
-3	3'(914) Depth
-4	4'(1219) Depth
-5	5'(1524) Depth
-6	6'(1829) Depth



NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



USA: T: (800) 338-2581 • Watts.com
Canada: T: (888) 208-8927 • Watts.ca
Latin America: T: (52) 55-4122-0138 • Watts.com

