For Commercial and Industrial Applications

Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No
Approval	Representative



G2 Series LFB6080-G2-SS, LFB6081-G2-SS

2-Piece, Full Port, Lead Free* Bronze Ball Valves with Stainless Steel Trim

Sizes: 1/4" - 4"

The G2-SS series ball vales are a 2-Piece, Full Port, Lead Free, Bronze valve with Stainless Steel trim. These products are ideal for potable water, commercial, and industrial applications. These valves features a blowout proof stem, as well as a full-port design which ensures minimal pressure drop. The G2-SS series offers multiple models for solder and NPT end-connections with NSF-61G certification.

Features

- Lead Free*, forged bronze body and adapter
- Full-port flow
- Full range of sizes from 1/4" 4"
- Certified to NSF/ANSI/CAN 61 & NSF/ANSI/CAN 372
- 316 Stainless steel ball and stem
- Minimal pressure drop due to large ports
- Blowout proof, pressure retaining stem
- Adjustable stem packing gland
- White handles for easy Lead Free* identification
- 100% Factory tested in USA

Models

- $\mbox{LFB6080}$ G2-SS $\mbox{$1/4"$}$ 4" 316 stainless steel ball and stem threaded NPT end connections
- LFB6081 G2-SS ¾" 3" 316 stainless steel ball and stem solder end connections

Please refer to watts.com for BAA information on specific models.

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.



Pressure - Temperature

Temperature Range:

0°F - 400°F (-18°C - 205°C) @ 50psi (3.4 bar)

Pressure Range:

- 1/4" 2" 600psi (41 bar) WOG, non-shock; 150psi (10.3 bar) WSP
- 21⁄2" 4 400psi (27.5 bar) WOG, non-shock; 125psi (8.6 bar) WSP

Specifications

A 2-piece full port Lead Free* bronze ball valve to be installed as indicated on the plans. Valves with top loaded stems or valves without adjustable packing are not acceptable. Pressure up to 600psi for 1/4" to 2" and 400psi for 21/2" to 4". The valve shall be constructed using Lead Free* bronze. Lead Free* ball valves shall comply with state codes and standards, where applicable, requiring reduced lead content. Valve must conform to NSF-61G and shall be a Watts Series LFB6080G2-SS (threaded) or LFB6081G2-SS (solder).

Standards

Tested and Certified by NSF International NSF-61 Potable Water and NSF 372 low lead. Complies with MSP-110



Applications

- Full range of fluids
- Hydronic Heating (90% glycol max)
- Low Pressure Steam, 15 psi max
- Not applicable for flammable gas installations
- Not compatible with soft annealed copper tubing

*The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.


NOTICE

For soldered versions, heat **MUST** be directed **AWAY** from the center of the valve body as excessive heat harm the seats. After soldering, the packing nut may have to be tightened.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.




Materials




Α.	Handle Nut	Zinc-plated carbon steel
В.	Handle Assembly	Zinc-plated carbon steel with vinyl
		insulator
C.	Packing Nut	Brass
D.	Stem Packing	Virgin PTFE
E.	O-ring	Fluorocarbon elastomer (FKM)
F.	Thrust Washer	Virgin PTFE
G.	Stem	316 Stainless Steel
Н.	Tag	Cardboard, Mylar coated both sides
١.	Body	Forged Lead Free* bronze
J.	Seats	Virgin PTFE
K.	Ball	316 Stainless Steel
L.	Adapter	Forged Lead Free* bronze

Temperature – Pressure



Dimensions – Weights



SIZE			DIMENSIONS						WEIGHT					
	C		H, H1		I		L		L1		LFB6080G2		LFB6081G2	
in	in	mm	in	mm	in	тт	in	mm	in	тт	lb	kg	lb	kg
1⁄4"	1 ¹³ ⁄16	46	37/16	87	7⁄16	11	13⁄4	47	-	-	0.4	0.2	-	-
3⁄8"	1 ¹³ ⁄16	46	37⁄16	87	1/2	13	11%	48.3	1 ¹⁵ ⁄16	49	0.4	0.2	0.4	0.18
1/2"	1 ¹³ ⁄16	46	37⁄16	87	1/2	13	2	57	21/8	54	0.5	0.22	0.4	0.18
3⁄4"	21/4	58	3 ¹⁵ ⁄16	101	3⁄4	19	21/4	58	3	76	0.9	0.41	0.8	0.36
1"	25/8	67	41⁄4	108	1	26	3	77	31/2	89	1.4	0.65	1.3	0.57
11⁄4"	2 ¹³ ⁄16	72	41⁄4	108	11/4	32	33/8	86	31/8	98	2.1	0.94	1.8	0.82
11⁄2"	3 ³ ⁄16	80	55/16	135	11/2	38	311/16	93	4 5⁄16	109	3.1	1.4	2.7	1.23
2"	31/2	89	6	153	2	51	4 ¹ / ₄	108	5 ³ ⁄8	136	4.9	2.25	4.4	2.02
2 ¹ /2"	4 ¹ /16	104	7 ³ /8	187	2 ¹ /2	63.6	5 ⁵ ⁄16	134	6 ¹ /4	158	9.0	4.1	8.2	3.7
3"	41/2	114	73⁄4	197	3	76.3	6 ¹ /16	154	73⁄/8	185	13.9	6.3	12.9	5.9
4"	5 ³ ⁄8	136	95/8	245	71/16	189	77/16	189	-	_	27.7	12.6	-	-

Ordering Chart

		Valve			Locking Handle Kit		Stem Extension				
	Ordering Code	Decription	Connection Type	EDP	Description	Size	EDP	Description	Size		
	0450115	1/4 LFB6080G2-SS	Threaded	88005484	#1 LL-HK LFB6080/1 G2-SS	Fits 1/4" - 1/2"	0789542	SXI-HK-1A StemExtension	1/4"-1/2" 3C/3CM1/G2		
	0450116	3/8 LFB6080G2-SS	Threaded	88005484	#1 LL-HK LFB6080/1 G2-SS	Fits 1/4" - 1/2"	0789542	SXI-HK-1A StemExtension	1/4"-1/2" 3C/3CM1/G2		
	0450117	1/2 LFB6080G2-SS	Threaded	88005484	#1 LL-HK LFB6080/1 G2-SS	Fits 1/4" - 1/2"	0789542	SXI-HK-1A StemExtension	1/4"-1/2" 3C/3CM1/G2		
	0450118	3/4 LFB6080G2-SS	Threaded	88005485	#2 LL-HK LFB6080/1 G2-SS	K LFB6080/1 G2-SS Fits 3/4" 07895		SXI-HK-9A StemExtension	3/4" 3C/G2		
2-SS	0450119	1 LFB6080G2-SS	Threaded	88005486	#3 LL-HK LFB6080/1 G2-SS	Fits 1" -1 1/4"	0789551	SXI-HK-10A StemExtension	1" - 1 1/4" 3C/G2		
LFB6080G2-SS	0450120	1 1/4 LFB6080G2-SS	Threaded	88005486	#3 LL-HK LFB6080/1 G2-SS	Fits 1" -1 1/4"	0789551	SXI-HK-10A StemExtension	1" - 1 1/4" 3C/G2		
LFB6	0450121	1 1/2 LFB6080G2-SS	Threaded	88005487	#4 LL-HK LFB6080/1 G2-SS	Fits 1 1/2"	0789552	SXI-HK-11A StemExtension	1 1/2" 3C/G2		
	0450122	2 LFB6080G2-SS	Threaded	88005488	#5 LL-HK LFB6080/1 G2-SS	Fits 2"	0789546	SXI-HK-5A StemExtension	2" 3C/3CM1/G2		
	0422015	2 1/2 LFB6080G2-SS	Threaded	88005490	#6 LL-HK LFB6080/1 G2-SS	Fits 2 1/2"	0789547	SXI-HK-6A StemExtension	2 1/2" 3C/3CM1/G2		
	0422016	3 LFB6080G2-SS	Threaded	88005491	#7 LL-HK LFB6080/1 G2-SS	Fits 3"	0789548	SXI-HK-7A StemExtension	3" 3C/3CM1/G2		
	0422017	4 LFB6080G2-SS	Threaded	88005492	#8 LL-HK LFB6080/1 G2-SS	Fits 4"	0789549	SXI-HK-8A StemExtension	4" 3C/3CM1/G2		
	0450123	3/8 LFB6081G2-SS	Solder	88005484	#1 LL-HK LFB6080/1 G2-SS	Fits 1/4" - 1/2"	0789542	SXI-HK-1A StemExtension	1/4"-1/2" 3C/3CM1/G2		
	0450124	1/2 LFB6081G2-SS	Solder	88005484	#1 LL-HK LFB6080/1 G2-SS	Fits 1/4" - 1/2"	0789542	SXI-HK-1A StemExtension	1/4"-1/2" 3C/3CM1/G2		
	0450125	3/4 LFB6081G2-SS	Solder	88005485	#2 LL-HK LFB6080/1 G2-SS	Fits 3/4"	0789550	SXI-HK-9A StemExtension	3/4" 3C/G2		
2-SS	0450126	1 LFB6081G2-SS	Solder	88005486	#3 LL-HK LFB6080/1 G2-SS	#3 LL-HK LFB6080/1 G2-SS Fits 1" -1 1/4" 0789551 SXI-HK-10A StemExtension		1" - 1 1/4" 3C/G2			
081G	0450127	1 1/4 LFB6081G2-SS	Solder	88005486	#3 LL-HK LFB6080/1 G2-SS	Fits 1" -1 1/4"	0789551	SXI-HK-10A StemExtension	1" - 1 1/4" 3C/G2		
LFB6081G2-SS	0450128	1 1/2 LFB6081G2-SS	Solder	88005487	#4 LL-HK LFB6080/1 G2-SS	Fits 1 1/2"	0789552	SXI-HK-11A StemExtension	1 1/2" 3C/G2		
	0450129	2 LFB6081G2-SS	Solder	88005488	#5 LL-HK LFB6080/1 G2-SS	Fits 2"	0789546	SXI-HK-5A StemExtension	2" 3C/3CM1/G2		
	0422021	2 1/2 LFB6081G2-SS	Solder	88005490	#6 LL-HK LFB6080/1 G2-SS	Fits 2 1/2"	0789547	SXI-HK-6A StemExtension	2 1/2" 3C/3CM1/G2		
	0422022	3 LFB6081G2-SS	Solder	88005491	#7 LL-HK LFB6080/1 G2-SS	Fits 3"	0789548	SXI-HK-7A StemExtension	3" 3C/3CM1/G2		

