

Engineering Specification

Job Name _____

Contractor _____

Job Location _____

Approval _____

Engineer _____

Contractor's P.O. No. _____

Approval _____


Representative _____

WD-H Series Grease Interceptor with Access Housing

Specification

Watts WD-H Series recessed epoxy coated steel grease interceptor with gasketed skid-proof cover secured with hex head center bolt(s), removable baffle assembly, deep seal trap with cleanout and air relief bypass, external vented flow control fitting, no hub (standard) connections, and epoxy coated steel access housing with skid-proof cover and adjustable carrier brackets.

Call customer service if you need assistance with technical details.



FLOW RATE	
SUFFIX	DESCRIPTION
7	7 GPM
10	10 GPM
15	15 GPM
20	20 GPM
25	25 GPM
35	35 GPM
50	50 GPM
75	75 GPM

OPTIONS	
SUFFIX	DESCRIPTION
-B	Sediment Bucket
-FC	Flange & Clamp Device
-O	Inlet & Outlet (other than standard)
-SS	All Stainless Steel

MODEL NO.	FLOW RATE GPM	Grease Cap. LBS.	Inlet & Outlet	B Base to Ctr.	C Top to Ctr.		D LENGTH	E WIDTH
					MIN.	MAX.		
WD-7-H	7	14	2"(51)	8 1/2"(216)	5 1/4"(133)	13 1/4"(337)	35"(889)	18 1/2"(470)
WD-10-H	10	20	2"(51)	8 1/2"(216)	5 1/4"(133)	13 1/4"(337)	39"(991)	19 1/2"(495)
WD-15-H	15	30	2"(51)	10 1/2"(267)	5 1/4"(133)	13 1/4"(337)	39"(991)	20 1/2"(521)
WD-20-H	20	40	3"(76)	11 1/2"(292)	5 1/4"(133)	13 1/4"(337)	41"(1041)	21 1/2"(546)
WD-25-H	25	50	3"(76)	12"(305)	6 1/4"(159)	14 1/4"(362)	43"(1092)	22"(559)
WD-35-H	35	70	3"(76)	14"(356)	6 3/4"(171)	14 3/4"(375)	47"(1194)	23 1/2"(597)
WD-50-H	50	100	4"(102)	16"(406)	7 1/4"(184)	15 1/4"(387)	49"(1245)	27 1/2"(699)
WD-75-H	75	150	4"(102)	18 1/2"(470)	7 3/4"(197)	15 3/4"(400)	53"(1346)	29 1/2"(749)

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



USA: T: (800) 338-2581 • Watts.com

Canada: T: (888) 208-8927 • Watts.ca

Latin America: T: (52) 55-4122-0138 • Watts.com