# **PURE WATER**

# Series PWS15 Water Softeners

**Watts Pure Water Series PWS15** water softeners are suitable for commercial applications ranging from 60,000 to 300,000 grains of hardness removal capacity at flow rates up to 55 gpm (208 lpm).



# **Operation of the Softener**

Hard water contains dissolved minerals in the form of Calcium (Ca), Magnesium (Mg), and Iron (Fe). An ion exchange process accomplishes removal of these minerals. Over a period of time, the resin will become exhausted and the softener will regenerate using a brine solution.

# **Softening Media**

The exchange media is a high-quality strong acid softener (cation) resin, WQA certified to NSF/ANSI Standard 61 with high whole bead count, no color throw, and is chlorine resistant. The media combines high-operating capacity with excellent chemical and physical stability for a long dependable life.

# **Regeneration Controller**

These softeners feature an electronic controller that combines simplicity with flexibility in a user-friendly package that is easy to setup and operate. A turbine flow meter provides accurate flow measurement and allows for efficient operation. Important operational information is stored in the timer which can be accessed for trouble shooting purposes.

#### **Control Valve**

The 1.5" brass control valve operates on command from the valve controller. Valve positioning is accomplished by a hydraulically balanced piston which glides effortlessly along non-corrosive spacers and seals to precise locations. This precision motor driven valve performs in the toughest applications, is WQA certified to NSF/ANSI standards 61 and 372, and is made of high-quality brass for a long reliable life.

#### Resin Tanks

All models feature corrosion resistant fiberglass tanks, with a thermoplastic inner liner. All tanks are certified by WQA or NSF to NSF/ANSI standards.

# **Brine System**

The brine tank is made of tough, high-density polyethylene. Brine tanks 18"-24" in diameter feature a grid plate for increased brine storage. A high-quality air check prevents air from entering the system.

#### **A WARNING**

Do not use with water that is microbiologically unsafe or of unknown quality without adequate disinfection before or after the system.



## **Specifications**

	MINERAL TANK			BRINE TANK		SOFTENING		LBS. SALT PER		FLOW RATE & PRESSURE		
MODEL NUMBER	TANK Size (in.)	RESIN Ft <sup>3</sup>	GRAVEL	TANK Size (in.)	SALT FILL	CAP Max	ACITY MIN	REGENEI MAX	RATION Min	SERV GPM	DROP PSI	BKW GPM
PWS15121C11	12x52	2.0	30 lbs.	18x40	400	60 K	40 K	30	12	15/20	15/25	4.0
PWS15121D11	14x65	3.0	60 lbs.	18x40	400	90 K	60 K	45	18	17/22	15/25	5.0
PWS15121E11	16x65	4.0	80 lbs.	18x40	400	120 K	80 K	60	24	25/40	15/25	7.0
PWS15121F11	18x65	5.0	100 lbs.	24x41	600	150 K	100 K	75	30	30/50	15/25	11.0
PWS15121G11	21x62	7.0	100 lbs.	24x50	800	210 K	140 K	105	42	35/53	15/25	13.0
PWS15121H11	24x72	10.0	200 lbs.	30x50	1400	300 K	200 K	150	60	40/55	15/25	15.0

## **Ordering Information**

MODEL NUMBER	DESCRIPTION	PIPE SIZE	SPACE Required D x W x H	WEIGHT LBS KGS	
PWS15121C11	2 Cubic Foot Simplex Softener with Flow Meter	1.5"	18 x 42 x 75	210	95
PWS15121D11	3 Cubic Foot Simplex Softener with Flow Meter	1.5"	18 x 44 x 87	240	109
PWS15121E11	4 Cubic Foot Simplex Softener with Flow Meter	1.5"	18 x 46 x 87	320	145
PWS15121F11	5 Cubic Foot Simplex Softener with Flow Meter	1.5"	24 x 50 x 87	380	172
PWS15121G11	7 Cubic Foot Simplex Softener with Flow Meter	1.5"	24 x 52 x 84	585	265
PWS15121H11	10 Cubic Foot Simplex Softener with Flow Meter	1.5"	39 x 60 x 96	710	322

#### Notes:

- Capacities are based on resin manufacturer's data and are dependent upon influent water TDS, temperature, bed depth, and flow rates. Feed water must be free of oil and color.
- Pipe size, tank size, and space requirements are in inches.
- Capacities and flow rates expressed above are per tank.
- Flow rates listed at 25 psi drops are for intermittent peak flow rates and are not to be used as continuous flows.

A Watts Water Technologies Company

S-WQ-PWS15 1526 © 2015 Watts