



Mercury (Hg) Testing for Water Testing

User Manual



Table of Contents

2	General Information.....	3
2.1	Qualitative Mercury Sensor	
2.2	Water Testing Guidelines	
2.3	Sensor and Cuvette Bag	
2.4	Inserting Cuvette and Sensor	
2.5	Sample Injection and Measurement	
2.6	Pipetting Use Guidelines	
3	Testing a Sample.....	9
3.1	Required Materials	
3.2	Testing a Sample	
3.3	Results	
3.4	Test for False Positive	
3.5	Test for False Negative	
4	Technical Specifications for ANDalyze Sensors.....	11
4.1	Detection in Drinking Water	
4.2	Interference	
4.3	Product Accuracy Ranges	
5	Consumables and Replacement Items.....	12
6	Customer Service Contact Information.....	13

2 General Information

Important: Before continuing, please read the entire AND1000 Fluorimeter User Manual. Pay attention to all danger, warning and caution statements. Failure to do so could result in serious injury to the operator or damage to the equipment. Make sure that the protection provided by this equipment is not impaired, do not use or install this equipment in any manner other than that specified in this manual. If the equipment is used in a manner not specified by the manufacturer, the protection provided by the manufacturer may be impaired.

2.1 Qualitative Mercury Sensor

The mercury sensor is a qualitative sensor that shows a Positive/Negative result. A “Positive” test result indicates that mercury is present at levels greater than 2 ppb. A “Negative” result indicates the water contains less than 2ppb mercury.

This test does not require on-site calibration.

Important: Certain levels of interfering ions may result in a false positive or false negative. Because of this, instructions to test for these are included below.

2.2 Water Testing Guidelines

Note: The below steps are for testing drinking water samples. These steps can also be used for other matrices such as surface, ground, industrial and wastewater which has been pre-treated. Contact ANDalyze customer service for additional application notes on pre-treatment methods.

Water Sampling

- For best results use freshly collected sample (unpreserved in acid) for analysis. We recommend that you use the sample within 1 hour (maximum of 2 hours) of collection to minimize any metal loss to the walls of the sample container.
- Once the sample is mixed with ANDalyze sample buffer, test within 15 minutes.

pH Range

The ANDalyze sample buffer that is provided in the sample tubes brings the pH of the test solution to pH 7.0. Generally, the raw sample water can be in the range of pH 5 – pH 8. If you have a sample which is acidic or basic, mix with the ANDalyze buffer and check the pH of this buffered test solution. It should be ~pH 7.0 for best results

Note: Our tests have shown that environmental samples preserved in acid to a pH < 2 cannot usually be brought to a pH of 7.0 when mixed with the ANDalyze buffer. These samples have to be first neutralized with NaOH to a pH ~5 before mixing with ANDalyze buffer. Please contact ANDalyze customer service for instructions related to pre-treatment of highly acidic or highly basic samples.

2.3 Sensor & Cuvette Bag

Sensor Bag: Each sensor bag contains a cuvette, a sensor and a desiccant. These are single use and must be discarded. The desiccant should be blue in color. If it has turned completely pink in color, sensor may not perform well.



2.4 Inserting Cuvette and Sensor

Cuvette: The cuvette has an arrow which should face you when inserted. Insert the cuvette completely so that the fluorimeter lid can close. The meter and cuvette design helps to prevent improper orientation. This is important as the path-length of the emission and detection should not change.

Sensor: The square portion of the sensor can be placed on the cuvette in any orientation with the round sections facing upward. Sensors can only be used once and should be disposed of immediately after use.



2.4 Sample Injection and Measurement

Fluorimeter instrument should be **laid flat** on a stable surface during a measurement.

A buffered solution is prepared in a sample tube as described in the test section (4) which is used for measurements.

A new syringe should be used to withdraw 1 mL water from a sample tube. This syringe can be attached to the top of the housing as shown in the picture.


The sample should be injected through the housing into the cuvette at a constant speed of **3 – 5 seconds**. The syringe and housing should be immediately removed and the sample door closed. The START button located just below the screen should be pressed to start any measurement.



2.5 Pipette Use Guidelines

1. **New Tip** – Attach a new tip by placing the end of the pipette into one of the available tips and pressing down on the pipette body.

Note: Tips are disposable and should never be used more than once. Use of tips helps prevent contaminating the pipette.




2. Depress the operating button on the top to the first stop (see photo at left). **DO NOT depress all the way to body.**
3. Immerse the clean tip into the solution to be withdrawn.
4. Release the pressure slowly to withdraw the solution into the tip.

Note: Make sure that the pipette tip continues to be immersed in the solution during release so as to not expose the tip point to air.

5. Remove the pipette from the solution.
6. Immerse the tip into the liquid present in the tube where the withdrawn solution is to be dispensed.
7. Slowly depress the operating button **ALL THE WAY** to dispense the liquid contained in the pipette tip. (See photo at right)
8. Remove the pipette and discard the used tip.

Note: Dispose of tips immediately after use to prevent possible contamination of pipette.



3 Testing a Sample

This section will walk you through the process of testing a water sample for the desired analyte. Please read this entire section before beginning the test as parts of the test will be time sensitive. Be aware and pay attention to all notes.

3.1 Required Materials

- AND1000 Fluorimeter
- (1) Sensor Bag with Sensor & Cuvette
- (1) Syringe
- (1) Buffer Solution Tube
- (1) Sample Cup (Not Provided)



Note: Before using the instrument assure that the fluorimeter device is charged. (See Section 4.1 in the User Manual for Battery Charging Information)

3.2 Testing a Sample

1. **Start-Up** - Initialize the instrument by pressing the ON/OFF button. Instrument will initialize in about 1-2 seconds.
2. **Metal Type** - Ensure that the fluorimeter is on the correct metal screen.
3. **Site** – Confirm that the site field is set at “None”.



Do Not press “Start” until the sample is ready!

4. **Pouch** - Open the black bag which contains the sensor (colored plastic housing) and plastic cuvette.


Important: The bag contains a transparent desiccant pouch. This should be blue in color. If desiccant has turned completely pink in color, sensor may not perform well.

5. **Cuvette** - Place the plastic cuvette in the instrument.
6. **Sensor** - Place colored plastic sensor on the cuvette. (Any orientation). Make sure sensor is seated securely on the cuvette.



Note: Unit may go into screen-saver mode after 2 minutes. Press any button to resume (Do not press and hold ON/OFF).

7. **Sample Tube** – Collect water to be tested in a clean cup (not provided).
8. Slowly pour the test water into the provided sample tube containing liquid buffer up to the 5 mL mark. If required, use one of the provided disposable plastic pipettes to transfer water accurately without exceeding 5 mL volume mark. Close cap tightly and mix well by shaking.



Important: Open tube carefully so that liquid buffer does not fall out. Do not exceed the 5 mL mark for accurate results.

9. **Syringe** - With one of the provided syringes, draw 1-ml of water from the sample tube into syringe.
10. Attach the syringe to the housing over the cuvette in the instrument. (Syringe tip will fit into top of sensor)



Note: If the unit is left on for more than 2 Minutes without any activity, a screen-saver (black screen) will be activated, press any button to resume operation (Do not press and hold ON/OFF). The instrument automatically turns off if not used for more than 10 minutes.

11. Maintaining a constant speed (over 3-5 seconds), carefully squeeze the sample water through the housing into the cuvette.
12. Quickly remove sensor housing and syringe and close sample chamber door.
13. Press the **START** button located just below the screen.
14. Remove cuvette when complete.

3.3 Results

The sample will be tested, and results will be displayed as positive or negative.

Note: A **Positive** result indicates that mercury is present above 2ppb. A **Negative** result indicates that the mercury level is below 2ppb (may be zero).

To save the results, press the **SAVE** button.



3.4 Test for False Positive

If your test result for mercury is positive, the validity can be tested by testing against a false positive by adding a mercury chelator and analyzing a chelated sample

Required Material

- AND1000 Fluorimeter
- (1) Sensor Bag with Sensor & Cuvette
- (1) Syringe
- (1) Buffer Solution Tube
- (1) Mercury Chelator pellet
- (1) Sample Cup (Not Provided)

In a new sample tube, add the test water up to the 5 mL mark as described before. To this add one pellet of the Mercury Chelator. Close the cap and shake well. Analyze 1 mL of the Chelator containing sample using a new mercury sensor.

Result: If the result of this sample containing Mercury Chelator is positive, this sample matrix may have led to a false positive. Contact ANDalyze customer service.



3.5 Test for False Negative

If your test result for mercury is negative, the validity can be tested by testing against a false negative.

Required Material

- AND1000 Fluorimeter
- (1) Sensor Bag with Sensor & Cuvette
- (1) Syringe
- (1) Buffer Solution Tube
- (1) 50 mL Tube (To be Re-used)
- Mercury Standard solution (1 ppm)
- (1) Sample Cup (Not Provided)

Prepare spiked sample: To one of the provided 50 mL tubes, add 50 mL of sample water. To this add 100 μ L of the provided mercury standard solution. Close the cap and shake well.

Add this spiked solution to a new sample tube up to the 5 mL mark. Shake well and analyze 1 mL of the sample using a new mercury sensor.

If the result of this spiked sample is negative, the sample matrix leads to false negatives due to interference. Contact ANDalyze customer service or test for mercury in a lab.



4 Technical Specifications for ANDalyze Sensors

4.1 Detection in Drinking Water

ANDalyze’s proprietary Catalytic DNA sensor uses a DNAzyme reaction that fluoresces in the presence of the target contaminant (lead, uranium, copper, mercury etc). The fluorescence of the reaction is measured using the AND 1000 fluorimeter to determine the concentration/ presence of the free analyte ion (Pb^{2+} , UO_2^{2+} , Cu^{2+} , Hg^{2+} etc.) in solution.

Materials Used

- Fluorimeter (Product: AND1000 Fluorimeter)
- Analyte Sensor Kit (Mercury100)
- Analyte/Metal Standard Solution



Sensor

Performance

Mercury dilutions containing 0 - 150 ppb Hg^{2+} were prepared in DI water. Five replicates were used for each test at each dilution.

Mercury Detection Range

2 – 50 ppb mercury

(Above 50 ppb mercury, there can be false negatives. If it is known that sample may contain very high levels of mercury, please dilute your sample in DI water).

4.2 Interference

Interference tests were done with a 0 or 1 ppb mercury in DI water plus the potential interfering ion. The interference tolerance levels represent the concentration above which there is a false positive for a 0 ppb mercury sample, or false negative where mercury is present. Data represents an average of at least three replicates.

Interfering ion	Interference level	Above tolerance level will cause:
Calcium, Ca^{2+}	80 ppm	False negative
Manganese, Mn^{2+}	100 ppm	False negative
Ammonium, NH_4^+	100 ppm	False negative
Copper, Cu^{2+}	0.5 ppm	False negative
Iron, Fe^{3+}	15 ppb	False negative
Aluminum, Al^{3+}	20 ppb	False negative
Magnesium, Mg^{2+}	30 ppm	False negative
Chloride, Cl^-	200 ppm	False negative
Sulfate, SO_4^{2-}	1500 ppm	False negative
Dihydrogen phosphate, $H_2PO_4^-$	2000 ppm	False negative
Bicarbonate, HCO_3^-	800 ppm	False negative
Zinc, Zn^{2+}	200 ppm	False positive
Cobalt, Co^{2+}	140 ppm	False positive
Cadmium, Cd^{2+}	60 ppm	False positive
Nitrate, NO_3^-	>10000 ppm	No interference
Sodium, Na^+	>3700 ppm	No interference

5 Consumables and Replacement Items

- Fluorimeter (Product: AND1000 fluorimeter)
 - o Includes Fluorimeter and USB to MINI-B Cable. Capable of measuring multiple metals.

- Sensor Kit (Products: Mercury100)
 - o Equipment for (25) Tests and (5) Calibrations
 - Kit Includes:
 - (30) Analyte Sensors
 - (30) Cuvettes
 - (30) Test Buffers
 - (35) Syringes
 - (15) Disposable Transfer Pipettes
 - 10 mL Mercury Standard Solution – 1 ppm Hg²⁺
 - Tube containing Mercury Chelator pellets
 - 100µL Automatic Pipette with Tips
 - (2) 50 mL tubes for testing false negatives
 - Instruction Manual
 - Material Safety Data Sheets (MSDS)

6 Customer Service Contact Information

Contact us by Email:

HFInfo@watts.com

By Telephone:

+1 888 203-7248 or 239-337-2116

Business Service Hours:

8:00am to 4:30pm Eastern Standard Time (USA)

Company Address:

HF scientific

3170 Metro Parkway

Ft. Myers, FL 33916-7597 USA

Website:

www.hfscientific.com

