Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No.
Approval	Representative

Series 1450F Iron Body Dual Controls

Size: 1/2"

Series 1450F iron body dual controls are designed to fill the boiler and system piping with water and to maintain water pressure in the system at all times. These valves also provide make up water to the system in the event of system leaks and come with an attached pressure relief valve set at 30psi (206.9 kPa). Series 1450F features a high capacity performance as well as unique simplified servicing accessibility for complete unitized maintenance.

Features

- Combination fill valve and safety pressure relief valve
- Choice of inlet connections (threaded, union solder or union threaded)
- Tight seating check valve
- Purge lever for manual purging
- High capacity
- Stainless steel strainer to protect the valve disc from fouling

Models

- 1450F Threaded inlet connection
- T1450F Union threaded inlet connection
- S1450F Union solder inlet connection

Specifications

A dual control valve shall be installed on the boiler or where indicated on the plans to fill boiler piping with water and to provide make up water in the event of system leaks. The regulator shall have high capacity performance and a simplified servicing design. The valve shall have an attached safety pressure relief valve set at 30psi. The dual control shall be a Watts Series 1450F.

Pressure - Temperature

Maximum Temperature: 212°F (100°C)

Maximum Working Pressure: 100psi (6.9 bar)

Adjustment Range: 10 – 25psi (68.7 – 172.4 kPa) set at 15psi (103.4 kPa)

Relief Valve Setting: 30psi (206.9 kPa)



Dimensions – Weights

MODEL	SIZE	DIMENSIONS						WEIGHT	
		A		В		C			
	in.	in.	mm	in.	mm	in.	mm	lbs.	kgs.
1450F	1/2	55/16	135	61/2	165	1%	41	3.3	1.5
T1450F	1/2	55/16	135	71/4	184	1%	41	3.3	1.5
S1450F	1/2	55/16	135	7	178	1%	41	3.3	1.5

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

NOTICE

Inquire with governing authorities for local installation requirements

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



USA: T: (978) 689-6066 • F: (978) 975-8350 • Watts.com Canada: T: (905) 332-4090 • F: (905) 332-7068 • Watts.ca Latin America: T: (52) 81-1001-8600 • Watts.com