Engineering Specification

Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No.
Approval	Representative

Dead Level® DX

Pre-Sloped Polypropylene Trench Drain System w/Ductile Iron Frame

Specification

Watts Dead Level® DX Pre-Sloped Trench Drain System with 12" wide x 48" long (standard) ductile iron frame, UV stabilized talc-filled polypropylene channels with 6" no hub bottom or end outlet(s). System shall be frame-anchored, with (specify) grating to suit DIN Class (specify) load rating. System to include frame connectors, grate lock-downs, and construction covers. Installation to be performed in accordance with manufacturer's installation instructions.

Call customer service if you need assistance with technical details.


Options		
Suffix	Description	
-B24	24" x 24" x 24" Catch Basin w/DI Grate	
-B24T	24" x 24" x 24" Catch Basin w/DI Grate & Trash Basket	
-B24SS	24" x 24" x 24" Catch Basin w/SS Grate	
-B24SST	24" x 24" x 24" Catch Basin w/SS Grate & Trash Basket	
-FG	Galvanized Steel Frame Guard	
-FS	Stainless Steel Frame Guard	
-0S	Outlet Strainer	
-VP	Vandal Proof Grate Lock-Downs	


NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.



Grate Options			
Suffix	Description	Class	
-DI	Ductile Iron	Class F 🗆	
-DI-ADA	Ductile Iron ADA	Class F \square	
-GDI	Galvanized Ductile Iron	Class F \square	
-RGP	Reinforced Galvanized Perforated	Class E \square	
-RGS	Reinforced Galvanized Slotted	Class E \square	
-RSP	Reinforced Stainless Steel Perforated	Class E \square	
-RSS	Reinforced Stainless Steel Slotted	Class E □	
-SCI	Solid Cast Iron	Class F □	





Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



USA: T: (800) 338-2581 • Watts.com Canada: T: (888) 208-8927 • Watts.ca

Latin America: T: (52) 55-4122-0138 • Watts.com

ES-WD-DeadLevel-DX 2503 © 2025 Watts