

## ACV Schematic

# LEAD FREE\*

## LFM114 (Globe) Rate-of-Flow Control Valve

### Features

- Throttles to maintain constant rate-of-flow
- Adjustable Closing Speed
- Orifice Plate Assembly is remote mounted (field installed)
- Rate-of-Flow setpoint is adjustable

### Standard Components

- 1 - Main Valve (M100 - Single Chamber)
- 2 - Rate-of-Flow Control
- 3 - Adjustable Closing Speed
- 4 - Orifice Plate Assembly
- X - Isolation Cocks


### Options and Accessories

- FC – Flo-Clean Strainer
- Y – Y-Strainer (Replaces Flo-Clean)
- AOS – Adjustable Opening Speed
- P – Position Indicator
- L – Limit Switch

### Operation

The ACV Rate-of-Flow Control Valve is designed to automatically limit flow rate to a constant, adjustable, maximum. It is controlled by a normally open, differential control pilot designed to: 1) Open (allowing fluid out of the main valve cover chamber) when the differential pressure across the orifice plate is below the adjustable set point, and, 2) Close (allowing fluid to fill the main valve cover chamber) when the differential pressure across the orifice plate is above the adjustable set point. A decrease in differential pressure causes the valve to modulate towards an open position, increasing flow rate. An increase in differential pressure causes the valve to modulate towards a closed position, decreasing flow rate.

The Orifice Plate Assembly should be installed three to five pipe diameters downstream of the Rate-of-Flow Valve, and field connected with  $\frac{3}{8}$ " minimum copper tubing in accordance with factory piping schematic. Please specify desired flow rate prior to ordering.



\*The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.

### NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.

# WATTS®

**USA:** Tel: (713) 943-0688 • Fax: (713) 944-9445 • Watts.com

**Canada:** Tel: (905) 332-4090 • Fax: (905) 332-7068 • Watts.ca

**Latin America:** Tel: (52) 81-1001-8600 • Fax: (52) 81-8000-7091 • Watts.com