Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No
Approval	Representative

Series 188A Anti-Siphon Vacuum Breaker For Irrigation Systems

Sizes: 3/4" - 2"

Series 188As are designed to protect drinking water supplies from backsiphonage of contaminated water in accordance with national plumbing codes and water authority requirements for non-potable service applications such as irrigation, fireline, or industrial processing. Features a lightweight, durable "disc float" suitable for temperatures up to 180°F (82°C) which closes the atmospheric vent to prevent spilling under all rates of flow. Upon downstream demand, the vent disc assembly rises, sealing the atmospheric vent, allowing water to flow. A loss of supply pressure or the creation of a negative supply pressure causes the vent disc assembly to drop, opening the atmospheric vent and closing the supply side of the valve. Contains a durable silicone disc which has high heat and water hammer shock resistance and ensures tight seating with the lightest of seating contacts.

Specifications

For Anti-Siphon Vacuum Breakers

An anti-siphon vacuum breaker shall be installed where indicated on the plans to prevent the backsiphonage of contaminated water. This device is not to be used under continuous pressure or where there is a possibility that a backpressure condition may develop. The device shall meet the requirements of A.S.S.E. Standard 1001, ANSI A112.1.1 and C.S.A. B64.Watts Series 188A.

Materials

Body:	Brass		
Internal Trim:	Bronze		
Seat Disc:	Silicone		
Disc Float:	Plastic		



188A

Approvals



1001 B64.1.1 Approved by the city of Los Angeles

Pressure – Temperature

Maximum Temperature: 180°F (82°C) Maximum Working Pressure: 125psi (8.6 bar)

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

NOTICE


Inquire with governing authorities for local installation requirements

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.




Installation


Atmospheric Vacuum Breaker must be installed 6" above the highest point of the downstream piping. There can be no shutoff valves downstream of an AVB. The AVB should not be subjected to continuous pressure for more than 12 hours per ASSE Std. 1001.



Capacities



Dimensions - Weights



SIZE	DIMENSIONS						WEIGHT	
	A		С		D			
in.	in.	mm	in.	mm	in.	mm	lbs.	kgs.
3/4	21/4	57	11 1%	48	1½	38	1.13	.51
1	21/8	73	21/8	54	1 ¹¹ ⁄16	43	1.75	.79
11⁄4	21/8	73	21/8	54	1 ¹³ ⁄16	46	2.13	.96
1½	35/8	92	27/16	62	2 ³ ⁄16	56	3.63	1.64
2	41/8	105	27/8	73	21/2	64	5.25	2.38

