For General Industrial and Plumbing Applications

Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No.
Approval	Representative

Series 6/P6 MIDI Check Valves

Series 6 will operate efficiently in silence all of the functions of a swing check or vertical lift check valve. These are not suggested for installation in sewage ejector piping.

Series P6 is a 1/4" NPT plastic check valve.

Features

Series 6

- Elastomer seat
- Installation in horizontal or vertical position
- Low pressure drop; low opening pressure
- Positive back stop
- Brass body

Series P6

- Plastic check valve
- Extremely low cracking pressure
- Full flow capabilities
- Bubble-tight seating
- Corrosion-resistant
- NSF approved grade acetal body

Applications

General Industrial and Plumbing OEM applications

A WARNING

Do not use for reciprocating air compressor service.

Pressure - Temperature

Series 6

Pressure: 200 psi (13.8 bars)

Maximum temperature: 180°F (82° C)

Series P6

Pressure: 235 psi (16.2 bars)

Maximum temperature: 150°F (66°C)

Sizes - Connections

NPT threaded connections

Series 6 Female X Female only

Sizes: 1/4", 3/8", 1/2", 3/4", 1"

Series P6 Sizes: 1/4"

To order P6 check valves, use the following:

01 for F x F (female x female) 02 for M x F (male x female)

Example: 1/4" P6-02



1/2" - 1" Watts 6

Watts P6 Series



Male x Male Watts P6



Female x Female Watts P6




Unique Positive Check Module




Dimensions - Weights

6 - Sizes: 1/4" - 3/8"




6 - Sizes: 1/2" - 1"




Direction of Flow

1/4" P6-01 - Female x Female



1/4" P6-02 - Male x Female



SIZE	MODEL	DIMENSIONS				WEIGHT	
		A		В			
in.		in.	mm	in.	mm	lbs.	kgs.
1/4		2	50	1	25	.31	.14
3/8		2	50	1	25	.31	.14
1/2	6	2	50	1	25	.31	.14
3/4		21/2	64	11/4	32	.63	.28
1		3	76	1½	38	.88	.40
1/4	P6 (01/02)	21//8	54	1	25	.31	.14

Cv RATING

SIZE	MODEL	ORII		
in.		in.	mm	Cv.
1/4		3/8	10	5.9
3/8		3/8	10	5.9
1/2	6	3/8	10	5.9
3/4		1/2	13	11.5
1		5/8	16	17.2
1/4	P6	3/8	10	5.9





