Engineering Specification

Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No.
Approval	Representative

Series 909RPDA

Reduced Pressure Detector Assemblies

Sizes: 21/2" - 10"

Series 909RPDA Reduced Pressure Detector Assemblies are used in health hazard applications and are designed exclusively for use in accordance with water utility authority containment requirements. It is mandatory to prevent the reverse flow of fire protection system substances, i.e., glycerin wetting agents, stagnant water and water of non-potable quality from being pumped or siphoned into the potable water line.

Benefits: Detects leaks . . . with emphasis on the cost of unaccountable water; incorporates a meter which allow the water utility to:

- · detect leaks that historically create great annual cost due to waste
- provide a detection point for unauthorized use. It can help locate illegal taps

Modular check design concept facilitates maintenance and assembly access. The coating on this backflow assembly uses ArmorTek™ technology to resist corrosion due to microbial induced corrosion (MIC) or exposed metal substrate. All sizes are standardly equipped with AWWA epoxy coated, UL/FM listed OSY resilient seated gate valves, CFM (cubic feet per minute) or GPM (gallon per minute) meter and ball type test cocks. A pressure differential relief valve is located in a zone between the check valves.

Modular Design


Features a modular design concept which facilitates maintenance and assembly access. All sizes are standardly equipped with gate valves and ball type test cocks.


Features

- Body construction fused epoxy coated cast iron
- Replaceable bronze seats
- Maximum flow at low pressure drop
- Compact for economy combined with performance
- Design simplicity for easy maintenance
- Utilizes advanced ArmorTekTM coating technology to resist corrosion of internals
- Furnished with 5/8" x 3/4" (16 x 19mm) meter
- Air-in/Water-out relief valve design provides maximum capacity during emergency conditions.
- No special tools required

Specifications


A Reduced Pressure Detector Assembly shall be installed on fire protection systems when connected to a public water supply. Degree of hazard present is determined by the local authority having jurisdiction. The unit shall be a complete assembly including UL listed and FM approved OSY shutoff valves. Including an auxiliary line consisting of an approved backflow preventer and water meter. The valve body shall utilize a coating system with built in electrochemical corrosion inhibitor and microbial inhibitor. The assembly shall meet the requirements of AWWA C511-92; ASSE 1047; UL Classified File No. EX3185; CSA B64 and USC Manual 8th. Edition. Assembly shall be a Watts Series 909RPDA.





How it operates

The unique relief valve construction incorporates two channels: one for air, one for water. When the relief valve opens, as in the accompanying air-in/water-out diagram, the right-hand channel admits air to the top of the reduced pressure zone, relieving the zone vacuum. The channel on the left then drains the zone to atmosphere. Therefore, if both check valves foul, and simultaneous negative supply and positive backpressure develops, the relief valve uses the air-in/water-out principle to stop potential backflow.



Now Available WattsBox Insulated Enclosures.

For more information, send for literature ES-WB.

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

NOTICE

Inquire with governing authorities for local installation requirements

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



Models

Suffix:

OSY - UL/FM outside stem and yoke resilient seated gate valves

CFM - cubic feet per minute meter

GPM – gallons per minute meter

LF - less shutoff valves

Materials

Discs: Rubber

Body: Epoxy coated cast iron Seat and Disc Holder: Bronze


Trim: Stainless steel Test Cocks: Bronze

Pressure - Temperature

Temperature Range: 33°F – 140°F (0.5°C – 60°C) continuous

Maximum Working Pressure: 175psi (12.1 bar)

Dimensions - Weights



NOTE: Piping for 3" 909 will start from #1 gate valve and connect at #2 check valve.

G (Open)

Standards

AWWA C511-92; CSA B64

USC Manual for Cross-connection Control, 8th Edition

Approvals






Approved by the foundation for Cross-Connection Control and Hydraulic Research at the University of Southern California.

Series 909AG AIR GAPS

When installing a drain line, use Series 909 air gaps on Model 909 backflow preventers.




Iron Body	Ordering	Series/Sizes			Dimen	sions			Weig	ght
Model	Code		l A	١	E	3	(С		
			in.	mm	in.	mm	in.	mm	lbs	kgs
909AG-F	0881378	1½" - 3" 009/909 1½" - 2" 009 M1 2" 009 M2	43%"	111	6¾	171	2	51	3.25	1.47
909AG-K	0881385	4" - 6" 909 8" - 10" 909 M1	6¾"	162	95%	244	3	76	6.25	2.83
909AG-M	0881387	8" – 10" 909	73/8"	187	111/4	286	4	102	15.50	7.03





SIZE	DIMENSIONS														WEI	WEIGHT						
	A		С		D		D1		E, E1		G		L		R		T		T1			
in.	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	lbs.	kgs.
21/2	411/4	1070	16%	416	51/4	133	41/4	114	12	305	7	178	261//8	664	14	356	9	229	75/8	194	230	104
3	421/4	1070	187//8	479	51/4	133	41/4	114	12	305	7	178	261//8	664	14	356	9	229	75/8	194	230	104
4	551//8	1400	223/4	578	6	152	57//8	149	17	432	91/2	241	37	940	15	381	135%	346	11¾	299	470	213
6	65½	1664	301//8	765	6	152	6	152	20¾	527	14½	368	45	1130	16	406	13%	346	11¾	299	798	362
8	78½	1994	37¾	959	93/4	248	85%	219	26	660	18½	470	551/4	1403	17	432	18½	470	16%	416	1456	660
10	93%	2378	45¾	1162	93/4	248	85//8	219	32	813	21½	546	67½	1715	18	457	18½	470	16%	416	2230	1012


Capacity


*Typical maximum flow rate (7.5 feet/sec.) **UL rated flow
















USA: T: (978) 689-6066 • F: (978) 975-8350 • Watts.com Canada: T: (888) 208-8927 • F: (905) 481-2316 • Watts.ca Latin America: T: (52) 55-4122-0138 • Watts.com

ES-909RPDA 2115 © 2021 Watts