

For Boiler Drain or Sill Cock Applications

Job Name _____
 Job Location _____
 Engineer _____
 Approval _____

Contractor _____
 Approval _____
 Contractor's P.O. No. _____
 Representative _____

Series BD-QT

Quarter-Turn Boiler Drains

Sizes: 1/2" - 3/4"

Series BD-QT quarter-turn boiler drains offer an innovative alternative to old-fashion multi-turn type boiler drains. These drains were developed to provide the speed and convenience of quarter-turn ball valve performance for boiler drain or sill cock applications.

For durability and extended length service, series BD-QT uses a rugged forged brass body, adjustable Teflon® stem packing and rugged aluminum tee handles. For added utility, the 1/2" model features a dual-pattern combination threaded and solder end by 3/4" hose connection. The 3/4" model is available in either solder or threaded ends.

Features

- Quarter-turn ball valve design
- Positive shutoff
- Rugged aluminum tee-handle design
- Adjustable Teflon® stem packing


Specifications

A quarter-turn boiler drain shall be installed where indicated on the plans. The boiler drain shall be manufactured from forged brass and have an adjustable Teflon® stem packing. The boiler drain shall feature a quarter-turn ball valve design and positive shutoff. The boiler drain shall be a Watts Series BD-QT.

Dimensions – Weights

MODEL	SIZE	DIMENSIONS						WEIGHT	
		A		B		C		lbs.	kg
	in.	in.	mm	in.	mm	in.	mm		
BD-QT	1/2	3 3/8	86	2 1/4	57	1 5/16	24	.04	.01
BD-QT	3/4	4 1/8	104	2 7/16	62	1 1/8	28	.05	.02

Teflon® is a registered trademark of E.I. DuPont de Nemours & Company Incorporated.




Materials

Body: Forged brass
 Stem Packing: Teflon®
 Tee Handle: Aluminum

Pressure-Temperature

Maximum Temperature: 250°F (121°C)
 Maximum Pressure: 200psi (13.8 bar)



NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



USA: T: (978) 689-6066 • F: (978) 975-8350 • Watts.com
 Canada: T: (905) 332-4090 • F: (905) 332-7068 • Watts.ca
 Latin America: T: (52) 81-1001-8600 • Watts.com