Engineering Specification

| Job Name — Con | ntractor ———— |
|----------------|---------------------|
| | oroval ———— |
| | ntractor's P.O. No. |
| | presentative ———— |

Series ET-RA

ASME

Pressurized Expansion Tanks for Heating and Cooling Systems

Models ET-RA 35 to ET-RA 2000

Watts Model ET-RA Tanks are ASME removable bladder type pre-charged expansion tanks. They are designed to absorb the expansion forces and control the pressure in heating and cooling systems. The water is contained in the heavy duty bladder preventing tank corrosion and waterlogging problems. ET-RA expansion tanks reduce tank sizes up to 80%.

Features

- Bladder Integrity Monitor
- ASME Section VIII Code Construction
- Removable Butyl Bladder
- Precharged to 12psi (Field Adjustable)

Construction

Shell: Carbon steel Bladder: Heavy duty butyl Prime Painted Exterior

Pressure - Temperature

Maximum Design Pressure: 125psig* (8.5 bar) Maximum Design Temperature: 240°F (115°C) Precharged to 12psi (83 kPa) *200 & 250psig available.

Specifications

Furnish and install as shown on plans a Watts Model ETRA ____gallon ____ " diameter x ____" (high) pre-charged steel expansion tank with a heavy duty butyl rubber bladder and Bladder Integrity Monitor. The tank shall have NPT system connections and a .302" - 32 charging valve connection (standard tire valve) to facilitate the on-site charging of the tank to meet system requirements. The tank must be constructed in accordance with Section VIII of the ASME Boiler and Pressure Vessel Code.

NOTICE

Inquire with governing authorities for local installation requirements



Schedule


| ACCEPTANCE | | | | | | | | |
|------------|-------------|---------|-------------|----------|--|--|--|--|
| MODEL NUM- | TANK VOLUME | VOLUME | ME TAGGING | | | | | |
| BER | GALLONS | GALLONS | INFORMATION | QUANTITY | | | | |
| ET-RA 35 | 10 | 10 | | | | | | |
| ET-RA 50 | 13 | 13 | | | | | | |
| ET-RA 85 | 23 | 23 | | | | | | |
| ET-RA 130 | 35 | 35 | | | | | | |
| ET-RA 200 | 53 | 53 | | | | | | |
| ET-RA 300 | 79 | 79 | | | | | | |
| ET-RA 400 | 106 | 106 | | | | | | |
| ET-RA 500 | 132 | 132 | | | | | | |
| ET-RA 600 | 158 | 158 | | | | | | |
| ET-RA 800 | 211 | 211 | | | | | | |
| ET-RA-1000 | 264 | 264 | | | | | | |
| ET-RA-1200 | 317 | 317 | | | | | | |
| ET-RA-1400 | 370 | 370 | | | | | | |
| ET-RA-1600 | 422 | 422 | | | | | | |
| ET-RA-2000 | 528 | 528 | | | | | | |

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.



ASME EXPANSION TANKS - Pressurized



Dimensions - Weight

| DIMENSIONS | | | | | | | | | | | | | | |
|--------------|-----|-----|------|-----|----|-----|----|----------------|-----|------|------|-----|---------|--------|
| Model Number | Α | | В | | C | D | | E | F | | G | | Weight* | |
| | in. | in. | mm | in. | mm | in. | mm | in. | in. | mm | in. | mm | lbs. | kgs |
| ET-RA 35 | 12 | 24 | 610 | 3/4 | 19 | 3/4 | 19 | .302" | 10 | 254 | _ | _ | 40 | 18.14 |
| ET-RA 50 | 14 | 24 | 610 | 3/4 | 19 | 3/4 | 19 | -32NC | 10 | 254 | _ | _ | 50 | 22.68 |
| ET-RA 85 | 16 | 37 | 940 | 1 | 25 | 3/4 | 19 | .302" | 12 | 305 | 51/2 | 140 | 90 | 40.82 |
| ET-RA 130 | 20 | 37 | 940 | 1 | 25 | 3/4 | 19 | | 16 | 406 | 51/2 | 140 | 125 | 56.7 |
| ET-RA 200 | 24 | 43 | 1092 | 1½ | 38 | 3/4 | 19 | | 20 | 508 | 51/4 | 133 | 210 | 95.25 |
| ET-RA 300 | 24 | 55 | 1397 | 1½ | 38 | 3/4 | 19 | | 20 | 508 | 51/4 | 133 | 225 | 102.06 |
| ET-RA 400 | 30 | 49 | 1245 | 1½ | 38 | 3/4 | 19 | -32NC | 24 | 610 | 51/4 | 133 | 300 | 136 |
| ET-RA 500 | 30 | 57 | 1448 | 1½ | 38 | 3/4 | 19 | | 24 | 610 | 51/4 | 133 | 335 | 151.95 |
| ET-RA 600 | 30 | 65 | 1651 | 1½ | 38 | 3/4 | 19 | | 24 | 610 | 51/4 | 133 | 360 | 163.29 |
| ET-RA 800 | 32 | 76 | 1930 | 1½ | 38 | 3/4 | 19 | | 28 | 711 | 51/4 | 133 | 475 | 215.46 |
| ET-RA 1000 | 36 | 76 | 1930 | 1½ | 38 | - | _ | .302" -32NC | 30 | 762 | - | _ | 552 | 250.38 |
| ET-RA 1200 | 36 | 88 | 2235 | 1½ | 38 | _ | _ | | 30 | 762 | - | _ | 679 | 307.99 |
| ET-RA 1400 | 36 | 100 | 2540 | 1½ | 38 | - | - | | 30 | 762 | _ | _ | 688 | 312.07 |
| ET-RA 1600 | 48 | 74 | 1880 | 1½ | 38 | - | - | | 42 | 1067 | _ | _ | 1046 | 474.46 |
| ET-RA 2000 | 48 | 86 | 2184 | 1½ | 38 | _ | _ | | 42 | 1067 | _ | _ | 1150 | 521.63 |

Note: Tanks are factory pre-charged at 12 psi and field adjustable. (*approximate)

Note: On models ET-RA 85 thru ET-RA 800 both top and bottom connections (C and D) access the bladder



USA: T: (978) 689-6066 • Watts.com **Canada:** T: (888) 208-8927 • Watts.ca

Latin America: T: (52) 55-4122-0138 • Watts.com

ES-ET-RA 2339 © 2023 Watts