

## For Commercial and Industrial Applications

Job Name \_\_\_\_\_

Contractor \_\_\_\_\_

Job Location \_\_\_\_\_

Approval \_\_\_\_\_

Engineer \_\_\_\_\_

Contractor's P.O. No. \_\_\_\_\_

Approval \_\_\_\_\_

Representative \_\_\_\_\_

# Series F127W

## Flanged High Capacity Water Pressure Reducing Valves

### Sizes: 3" – 4" (80 – 100mm)

Series F127W Flanged High Capacity Water Pressure Reducing Valves are designed to reduce incoming water pressure to a sensible level to protect plumbing system components and reduce water consumption. The F127W is a remote control type regulator ideal for commercial and industrial applications where a regulator must reach full capacity with a minor drop in reduced pressure. This series is also suitable for applications where close pressure regulation is required through extensive volume demand. This series is suitable for water supply pressures up to 175psi (12.1 bar) and may be adjusted from 25 – 100psi (172 – 690 kPa). All parts are quickly and easily serviceable.


### Features

- Replaceable stainless steel seat
- Outstanding maintenance features
- Close control of reduced pressure
- High temperature-resisting diaphragm
- Interchangeable diaphragm chamber
- Iron body triple coated with special corrosion preventative materials superior to hot dip galvanizing

### Specifications

A Water Pressure Reducing Valve shall be installed on the water service pipe near its entrance to the building where supply main pressure exceeds 60psi (413 kPa) to reduce it to 60psi (413 kPa) or lower. The valve shall be equipped with a  $\frac{3}{8}$ " (10mm) tapping to receive equalizer piping and a  $\frac{3}{4}$ " (20mm) tapping to receive auxiliary regulator piping for low flow requirements. Valve shall be a Watts Series F127W.

4" (100mm) F-127W



## Materials

Body: Iron  
 Seat: Replaceable stainless steel  
 Stem: Stainless steel


## Pressure – Temperature

Temperature Range: 33°F – 160°F (0.5°C – 71°C)  
 Maximum Working Pressure: 175psi (12.1 bar)  
 Adjustable Reduced Pressure Range: 25 – 100psi  
 (172 – 690 kPa)

## Options (4" size only)


WR 3/4" (20mm) Model 223 auxiliary regulator.  
 (Piping not included)

## Option WR



## Dimensions – Weights

SIZE (DN)		Connection	DIMENSIONS						WEIGHT	
in.	mm		A		C		D		lbs.	kgs.
3"	80	flanged	8	203	16 3/4	425	3 3/4	95	42	19
4"	100	flanged	12 1/8	308	16 3/4	425	4 1/2	114	84	38



A Watts Water Technologies Company



USA: Tel. (978) 688-1811 • Fax: (978) 794-1848 • www.watts.com  
 Canada: Tel. (905) 332-4090 • Fax: (905) 332-7068 • www.wattscanada.ca