# For Water Heater/Tank Applications

Contractor \_

Contractor's P.O. No.

Representative \_

Approval

Job Name \_

Job Location \_

Engineer \_

Approval \_



# Model LFN36-M1 Vacuum Relief Valve

### Sizes: 1/2" - 3/4" Male NPT

#### **Features**

- Low profile
- All Lead Free\* brass body
- Protective cap
- Suitable for low pressure steam and water service
- Tested and rated to ANSI Z21.22
- CSA certified
- The LFN36-M1 features Lead Free\* construction to comply with Lead Free\* installation requirements.

### Applications

- Domestic water heaters and supply tanks
- Table top heaters
- Jacketed steam kettles
- Unit heaters
- Low pressure steam systems
- Steam coil heaters

**Note:** Vacuum relief valves are not designed or approved as backsiphonage backflow preventers. For protection against backsiphonage install Watts Series 288A vacuum breakers.

### Standards

Tested and rated to ANSI Z21.22 CSA certified

### **Specifications**

A Watts Model LFN36-M1 Vacuum Relief Valve shall be installed on domestic hot water supply tanks/ heaters/ unit heaters/ steam kettles as indicated on plans. The vacuum relief valve shall be ANSI Z21.22 rated and CSA certified. The vacuum relief valve shall have an all brass body and include a protective cap for automatic venting of a closed system to atmosphere when a vacuum is created. The Lead Free\* Vacuum Relief Valve shall comply with state codes and standards, where applicable, requiring reduced lead content. The Watts LFN36-M1 Vacuum Relief Valve permits air to enter and prevent vacuum conditions that could siphon the water from the system, resulting in collapse of a tank or water heater or equipment burn out. The valve shall be a Watts Model LFN36-M1.




Design certified by



LFN36-M1

Tested and rated under "ANSI Z21.22 Relief Valves for Hot Water Supply Systems".



Domestic Hot Water Supply Tanks and Heaters with Top Supply

#### NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

#### NOTICE


Inquire with governing authorities for local installation requirements

\*The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.




## Materials



# Pressure – Temperature

Maximum steam working pressure: 15 psi (1.03 bar) Maximum temperature: 250°F (121°C)

## **Dimensions-Weights**



SIZE		DIMEN	WEIGHT			
		A	В			
in.	in.	тт	in.	тт	0Z.	gr
1/2	2	50	2	50	4	113
3⁄4	2	50	2	50	4	113

## Capacity

SIZE	MODEL	VENTING CAPACITY	
in.		CFM	LPM
1/2	LFN36-M1	15	425
3/4	LFN36-M1	15	425



