SPECIFICATION SECTION XXX

PRODUCT: TWIN ALTERNATING SODIUM REGENERATED ION EXCHANGE WATER SOFTENER

1.0 GENERAL

Furnish a twin alternating sodium regenerated water softener as specified here in this section and as called for in the equipment schedule for the reduction of water hardness. The water softener shall be supplied complete, and assembled entirely by one manufacturer. System to include all components required for proper operation of the system. These components include mineral tanks, ion exchange resin, gravel under-bedding, internal distributor system, twin alternating control valve, meter, back wash flow control, and brine tank with air check. Expressed grain capacity of the system is per media tank. The system shall be a Watts Pure Water brand model number PWS______ manufactured by Watts.

2.0 RELATED SECTIONS XXX

3.0 COMPONENTS

3.1 Mineral Tanks

The mineral tanks shall be constructed of a polypropylene liner with a continuous roving outer fiberglass reinforced wrapping. The tank shall be Non-ASME code with a 150 psi maximum pressure rating, 120 deg. F (48 deg. C) maximum temperature rating, and certified to NSF/ANSI Standard 44 or 61. 14" diameter and larger shall have a bottom base permanently installed with industrial grade adhesive. The tanks will come with a 2.5" or a 4" threaded port at the top for loading media and connection of the control valve. The tanks shall be designed with a safety factor of 4:1 for minimum burst pressure.

3.2 Ion Exchange Resin

The ion exchange resin shall be a high purity, premium grade, strongly acidic gel-type cation exchange resin specially designed for drinking water treatment and certified to NSF/ANSI Standard 61 and 372. The ion exchange resin shall be composed of polystyrene with 8% divinylbenzene crosslinking that offers excellent bead integrity, high resistance to bead fracture or osmotic shock, and very low extractables. The resin shall have a light amber color and shall be specially pretreated to remove taste, odor and color throw. Resin bead size shall be 16X40 mesh. The resin shall meet the requirements of FDA regulation CFR section 21, §173.25. Maximum grain capacity

per cubic foot of resin shall be 30,000 grains as CaCO3 when regenerated with 15 lbs of sodium chloride and 20,000 grains as CaCO3 when regenerated with 6 lbs of sodium chloride. PH stability of the resin must be 0-14. Temperature stability of the resin must be up to 250 deg. F (121 deg. C).

3.3 Gravel Under-bedding

The gravel under-bedding shall be a flint media. This media shall be washed to rid it of fines to prevent clogging of the lower distributor system. Enough gravel must be furnished to completely cover the lower distributors in the mineral tanks.

3.4 Internal Distributor System

The internal distributor system shall come already installed in the water softener mineral tank(s). The screens/laterals of the internal distribution system shall be a slotted screen type diffuser. The slot cross section shall be a V shape to promote a self-cleaning characteristic of the slot. Slot size shall be .008" and not allow the resin to pass through and become present in the systems effluent water. The lower distributor shall be a hub and lateral design for mineral tanks over 24" in diameter and a single point design for mineral tanks 24" in diameter and below. Lateral type screen will have an internal perforated pipe core to evenly distribute water flow across the entire lateral to prevent resin bed channeling. The internal distributor system screens shall be made of abrasion resistant 20% glass filled polypropylene. The distributor tube connecting the internal distribution system to the system control valve shall be made of polyvinyl chloride.

3.5 System Control Valve

The system control valve shall control all functions of the water softener regeneration and service cycles. One control will operate both tanks. The control valve shall be a multi-port type constructed of lead free brass as defined in the US EPA Safe Drinking Water Act and be tested and certified to NSF/ANSI STD. 61 Section 8 Material Safety Only and NSF/ANSI STD. 372 for Lead Free compliance. Cycle positioning shall be motor driven, slow in actuation, and not cause pressure surges or water hammer. The system control valve shall be furnished with a fully programmable microprocessor based controller. Operating data for the system shall be displayed on the controller LCD screen. Operating data shall be current cycle step during regeneration, time of day, service gallons remaining, tank in service, water flow indicator, and current error codes. System programming shall be stored in the controller memory and not be lost due to power outages. The controller, related wiring, and positioning motors shall be housed within an enclosure with a clear window so

that the user can view the status of the system controller. The control valve shall be supplied with a meter capable of tracking gallons higher and lower than the system is capable of processing so that it is not a flow restriction at high flow rates or not sensitive to low flow rates. A drain line flow control shall be provided to regulate the flow of water to drain during a regeneration cycle. The flow controller shall be constructed of a sch. 80 PVC nipple or brass coupling with an orifice plate in the middle. Pressure sensitive rubber flow restrictors shall be installed in the orifice plate. These flow restrictors shall not be able to wash out of the plate and shall allow the consistent passage of water with pressure fluctuations between 30 to 100 psi.

3.6 Brine Tank

Provide a brine tank made of high density polyethylene for making a brine solution for the water softener to use during a regeneration cycle and for salt storage. The brine tank shall be furnished with an over flow connection, lid, aircheck, and brine well. The brine tank shall be sized to hold enough salt for 12 regenerations at 6 lbs of salt per cubic foot of resin.

3.7 Test Kit

Provide a Watts model T10460 hardness test kit to the owner upon start up of the system.

4.0 SERVICES

4.1 Warranty

The Contractor providing the equipment shall provide a 1 year parts and labor warranty for the system to protect against manufacturers defects. The system shall not be subjected to water temperatures above 110 deg. F (43 deg. C) or below 34 deg. F (1 deg. C). nor shall it be subjected to pressure exceeding 125 psi. During operation the feed water pressure must not fall below 25 psi so a proper regeneration can be performed. The resin shall not be subjected to iron levels greater than 1 ppm or free chlorine greater than 1 ppm. The resin attrition shall not be more than 3% per year.

4.2 Start Up

The Contractor providing the equipment shall provide start up of the water softener system, ten 50 lb bags of pellet form sodium chloride for the brine tank, and perform a training for the owner upon completion of start up.