For Commercial Applications

Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No.
Approval	Representative

Series N170 Hot Water Master Tempering Valves

Watts Series N170 hot water master tempering valves are especially designed for use on larger hot water supply systems for mixing hot and cold water for a variety of applications to extend the hot water supply. This series uses paraffin-based thermostat to sense and adjust outlet temperature.

Features

- ASSE 1017 and IAPMO cUPC Listed
- N170-M3 uses paraffin-based thermostat to sense and adjust outlet temperature
- Dirt and lime resistant poppet and seat design
- Virtual shutoff if supply pressure fails
- Vandal-resistant locking mechanism to secure temperature setting
- · Factory tested



Specifications

Maximum Operating Pressure	
Maximum Hot Water Temperature	
Minimum Hot Water Supply Temperature	nt*
Temperature Adjustment Range** 90 - 180°F (32 - 82°C)	
Hot Water Inlet Temperature Range 120 - 180°F (42 - 82°C)	
Cold Water Inlet Temperature Range	
Listing ASSE 1017, IAPMO cUP	С
Approval Standards ASSE 1017, CSA B125.3	3

*With Equal Pressure

**Low Limit cannot be less than the cold water temperature. For best operation, hot water should be at least 5°F (3°C) above desired set point.

A WARNING

Watts Hot Water Master Tempering Valves cannot be used for tempering water temperature at fixtures. Severe bodily injury (i.e., scalding or chilling) and/or death may result depending upon system water pressure changes and/or supply water temperature changes. ASSE standard 1016, 1069 or 1070 listed devices such as Watts Series MMV, USG, and L111 valves should be used at fixtures to prevent possible injury.

The Watts Hot Water Tempering Valves are designed to be installed at or near the boiler or water heater. They are not designed to compensate for system pressure fluctuations and should not be used where ASSE standard 1016, 1069 or 1070 devices are required. These Watts valves should never be used to provide "anti-scald" or "anti-chill" service.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



Capacity

Dimensions

Flow Capacity at 50-50 mixed Less Checkstops													
			Pressure Drop Across Valve										
Model	Inlet / Outlet	Min. Flow	Cv	5psi	10psi	20psi	30psi	45psi	60psi				
INIDUCI	(NPT)	to ASSE 1017	υv	(34 kPa)	(69 kPa)	(138 kPa)	(207 kPa)	(310 kPa)	(414 kPa)				
³ /4" N170-M3	³ /4 X ³ /4"	3 gpm	6.70	15 gpm	21 gpm	30 gpm	37 gpm	45 gpm	52 gpm				
°74 NT7U-WIS	3/4 X 3/4	11 lpm	0.70	57 lpm	79 lpm	114 lpm	140 lpm	170 lpm	197 lpm				
1" N170-M3	1 x 1"	4 gpm	10.13	23 gpm	32 gpm	45 gpm	56 gpm	68 gpm	79 gpm				
1 1170-103		15 lpm	10.15	87 lpm	121 lpm	170 lpm	212 lpm	257 lpm	299 lpm				
1 ¹ /4" N170-M3	1- ¹ /4 x 1- ¹ /4"	4 gpm	14.16	32 gpm	45 gpm	63 gpm	76 gpm	95 gpm	110 gpm				
1 74 N170-WIS		15 lpm	14.10	121 lpm	170 lpm	238 lpm	288 lpm	360 lpm	416 lpm				
11/	1- ¹ / ₂ x 1- ¹ / ₂ "	5 gpm	15.65	35 gpm	49 gpm	70 gpm	86 gpm	105 gpm	121 gpm				
1 ¹ /2" N170-M3		19 lpm	15.05	134 lpm	185 lpm	265 lpm	326 lpm	397 lpm	458 lpm				
2" N170-M3	0 x 1 1/ x 0	7 gpm	18.63	42 gpm	59 gpm	83 gpm	102 gpm	125 gpm	144 gpm				
	2 x 1-1/2 x 2"	26 lpm	10.05	159 lpm	223 lpm	314 lpm	386 lpm	473 lpm	545 lpm				



	I	Flow Capac	ity at 50	-50 mixed	d with Ch	eckstops							
			Pressure Drop Across Valve										
Model	Inlet / Outlet	Min. Flow	0	5psi	10psi	20psi	30psi	45psi	60psi				
Wouei	(NPT)	to ASSE 1017	Cv	(34 kPa)	(69 kPa)	(138 kPa)	(207 kPa)	(310 kPa)	(414 kPa)				
3/4" N170-M3 CSUT	³ / ₄ x ³ / ₄ "	3 gpm	6.26	14 gpm	20 gpm	28 gpm	34 gpm	42 gpm	48 gpm				
3/4" N170-W3 6501		11 lpm	0.20	53 lpm	76 lpm	106 lpm	129 lpm	159 lpm	182 lpm				
1" N170-M3 CSUT	³ /4 x 1"	4 gpm	9.54	21 gpm	30 gpm	43 gpm	52 gpm	64 gpm	74 gpm				
1 1170-113 6301		15 lpm	9.04	79 lpm	114 lpm	163 lpm	197 lpm	242 lpm	280 lpm				
1 ¹ /4" N170-M3	1- ¹ /4 x 1- ¹ /4"	4 gpm	13.42	30 gpm	42 gpm	60 gpm	74 gpm	90 gpm	104 gpm				
CSUT		15 lpm	13.42	114 lpm	159 lpm	227 lpm	280 lpm	341 lpm	394 lpm				
1 ¹ /2" N170-M3	1-1/4 x 1-1/2"	5 gpm	14.90	33 gpm	47 gpm	67 gpm	82 gpm	100 gpm	115 gpm				
CSUT	1-'/4 X 1-'/2	19 lpm	14.90	125 lpm	128 lpm	254 lpm	310 lpm	379 lpm	435 lpm				
2" N170-M3 CSUT	1-1/4 x 2"	7 gpm	17.89	40 gpm	57 gpm	80 gpm	98 gpm	120 gpm	139 gpm				
	1-'/4 X Z	26 lpm	17.09	151 lpm	216 lpm	303 lpm	371 lpm	454 lpm	526 lpm				



MODEL	BODY INLETS	CHECKSTOP	BODY OUTLET	DIMENSIONS												WEI	GHT			
	NPT	INLETS NPT	NPT																	
				A	1	В	С	D		E	F		G		Н		J			
				in. mm	in.	тт	in. mm	in.	тт	in. mm	in.	тт	in.	тт	in.	тт	in.	тт	lbs.	kgs.
3⁄4 N170-M3	3⁄4	N/A	3/4	N/A	41/2	114	N/A	31/2	89	N/A	1 7⁄16	36	35/8	92	47⁄8	124	2 ¹⁵ /16	75	4.8	2.2
3/4 N170-M3 CSUT	N/A	3⁄4	3⁄4	9¼ 235	4 ½	114	11 ⁷ /16 291	31/2	89	1 ¹³ ⁄16 46	1 ½16	36	35/8	92	47⁄8	124	2 ¹⁵ /16	75	9.8	4.5
1 N170-M3	1	N/A	1	N/A	4%16	116	N/A	31/2	89	N/A	1 ½16	36	35/8	92	47⁄8	124	2 ¹⁵ /16	75	4.8	2.2
1 N170-M3 CSUT	N/A	3⁄4	1	101/8 264	4%16	116	121/16 319	31/2	89	1 ¹³ /16 46	17/16	36	35/8	92	47⁄8	124	2 ¹⁵ /16	75	10.3	4.9
1¼ N170-M3	1¼	N/A	1¼	N/A	6 ¹ /16	154	N/A	37⁄16	87	N/A	1¾	44	3 ¹¹ / ₁₆	94	5¼	133	4½	114	9.4	4.3
11/4 N170-M3 CSUT	N/A	1¼	11⁄4	12¹/ 16 306	6 ¹ /16	154	151/16 383	37⁄16	87	21⁄2 64	1¾	44	3 ¹¹ / ₁₆	94	51⁄4	133	41⁄2	114	19.3	8.8
11/2 N170-M3	1½	N/A	1½	N/A	6 ¹ / ₁₆	154	N/A	37/16	87	N/A	1¾	44	3 ¹¹ / ₁₆	94	51⁄4	133	41/2	114	9.1	4.1
11/2 N170-M3 CSUT	N/A	1¼	1½	13¼ 337	6 ¹ /16	154	16¼ 413	37⁄16	87	2½ 64	1¾	44	3 ¹¹ / ₁₆	94	5¼	133	4½	114	19.8	9.0
2 N170-M3	2 (Hot) 11/2 (Cold)	N/A	2	N/A	67/16	164	N/A	3 ³ ⁄16	81	N/A	2 ¹ /16	52	31/8	98	53/8	137	41⁄2	114	10.4	4.7
2 N170-M3 CSUT	N/A	11⁄4	2	13¾ 349	67/16	164	16¾ 425	3 ¾16	81	21/2 64	2 ¹ /16	52	31/8	98	53%	137	41⁄2	114	21.3	9.7

Typical Specification

Master mixing valve shall feature paraffin-based, thermal actuation technology for precise temperature control. Valve shall be listed to ASSE 1017 and cUPC and shall be approved to ASSE 1017 & CSA B125.3 standards. Master mixing valve shall have an approach temperature of 5° F (3°C). Valve shall have an outlet temperature range from 90 – 180°F (32 to 82°C) with a lockable temperature-setting feature. Valve shall be manufactured of corrosion resistant materials and feature a single-

seat design for positive shutoff. Minimum flows to ASSE 1017 shall be $^{3/_4}$ N170-M3 (3.0 gpm, 11 lpm), 1 N170-M3 (4.0 gpm, 15 lpm), 1-1/4 N170-M3 (4.0 gpm, 15 lpm), 1-1/2 N170-M3 (5.0 gpm, 19 lpm), 2 N170-M3 (7.0 gpm, 26 lpm).

Master mixing valves shall be of Watts Series N170-M3. Any alternate must have a written approval prior to bidding.





A Watts Water Technologies Company

USA: 815 Chestnut St., No. Andover, MA 01845-6098; www.watts.com Canada: 5435 North Service Rd., Burlington, ONT. L7L 5H7; www.wattscanada.ca