# For Commercial Applications

Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No.
Approval	Representative



# Series LFN170 Hot Water Master Tempering Valves

Watts Series LFN170 hot water master tempering valves are especially designed for use on larger hot water supply systems for mixing hot and cold water for a variety of applications to extend the hot water supply. This series uses paraffin-based thermostat to sense and adjust outlet temperature. The LFN170s feature Lead Free\* construction to comply with Lead Free\* installation requirements.

## Features

- Lead Free\* brass body construction
- ASSE 1017 and IAPMO cUPC Listed
- LFN170-M3 uses paraffin-based thermostat to sense and adjust outlet temperature
- Dirt and lime resistant poppet and seat design
- Virtual shutoff if supply pressure fails
- Vandal-resistant locking mechanism to secure temperature setting
- Factory tested

## **Specifications**

Maximum Operating Pressure125psig (861 kPa)Maximum Hot Water Temperature200°F (93°C)Minimum Hot Water5°F (3°C) Above Set Point\*\*Supply Temperature90 - 180°F (32 - 82°C)Temperature Adjustment Range\*\*\*90 - 180°F (42 - 82°C)Hot Water Inlet Temperature Range120 - 180°F (42 - 82°C)Cold Water Inlet Temperature Range40 - 80°F (4 - 27°C)ListingASSE 1017, IAPMO CUPCApproval StandardsASSE 1017, CSA B125.3

\* The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.

- \*\* With Equal Pressure
- \*\*\* Low Limit cannot be less than the cold water temperature. For best operation, hot water should be at least 5°F (3°C) above desired set point.



#### A WARNING

Watts Hot Water Master Tempering Valves cannot be used for tempering water temperature at fixtures. Severe bodily injury (i.e., scalding or chilling) and/or death may result depending upon system water pressure changes and/or supply water temperature changes. ASSE standard 1016, 1069 or 1070 listed devices such as Watts Series LFMMV, LFUSG, or LFL111 valves should be used at fixtures to prevent possible injury.

The Watts Hot Water Tempering Valves are designed to be installed at or near the boiler or water heater. They are not designed to compensate for system pressure fluctuations and should not be used where ASSE standard 1016, 1069 or 1070 devices are required. These Watts valves should never be used to provide "anti-scald" or "anti-chill" service.

#### NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

#### NOTICE

Inquire with governing authorities for local installation requirements

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



## Capacity

### Dimensions

Flow Capacity at 50-50 mixed Less Checkstops													
			Pressure Drop Across Valve										
Model	Inlet / Outlet	Min. Flow	Cv	5psi	10psi	20psi	30psi	45psi	60psi				
WOUGI	(NPT)	to ASSE 1017	UV	(34 kPa)	(69 kPa)	(138 kPa)	(207 kPa)	(310 kPa)	(414 kPa)				
<sup>3</sup> /4" LFN170-M3	<sup>3</sup> /4 X <sup>3</sup> /4"	3 gpm	6.70	15 gpm	21 gpm	30 gpm	37 gpm	45 gpm	52 gpm				
9/4" LFN170-W3	0/4 X 0/4	11 lpm	0.70	57 lpm	79 lpm	114 lpm	140 lpm	170 lpm	197 lpm				
1" LFN170-M3	1 x 1"	4 gpm	10.13	23 gpm	32 gpm	45 gpm	56 gpm	68 gpm	79 gpm				
I LENITO-WIS		15 lpm	10.15	87 lpm	121 lpm	170 lpm	212 lpm	257 lpm	299 lpm				
1 <sup>1</sup> /4"	41/. v 41/.0	4 gpm	14.16	32 gpm	45 gpm	63 gpm	76 gpm	95 gpm	110 gpm				
LFN170-M3	1 <sup>1</sup> / <sub>4</sub> x 1 <sup>1</sup> / <sub>4</sub> "	15 lpm	14.10	121 lpm	170 lpm	238 lpm	288 lpm	360 lpm	416 lpm				
<b>1</b> <sup>1</sup> /2"	1 <sup>1</sup> /2 x 1 <sup>1</sup> /2"	5 gpm	15.65	35 gpm	49 gpm	70 gpm	86 gpm	105 gpm	121 gpm				
LFN170-M3	1.72 X 1.72	19 lpm	15.05	134 lpm	185 lpm	265 lpm	326 lpm	397 lpm	458 lpm				
2" LFN170-M3	2 x 1 <sup>1</sup> / <sub>2</sub> x 2"	7 gpm	18.63	42 gpm	59 gpm	83 gpm	102 gpm	125 gpm	144 gpm				
	Z X 1 1/2 X Z	26 lpm	10.03	159 lpm	223 lpm	314 lpm	386 lpm	473 lpm	545 lpm				



	Flow Capacity at 50-50 mixed with Checkstops													
			Pressure Drop Across Valve											
Model	Inlet / Outlet	Min. Flow	•	5psi	10psi	20psi	30psi	45psi	60psi					
Model	(NPT)	to ASSE 1017	Cv	(34 kPa)	(69 kPa)	(138 kPa)	(207 kPa)	(310 kPa)	(414 kPa)					
3/4" LFN170-M3	<sup>3</sup> /4 x <sup>3</sup> /4"	3 gpm	6.26	14 gpm	20 gpm	28 gpm	34 gpm	42 gpm	48 gpm					
CSUT		11 lpm	0.20	53 lpm	76 lpm	106 lpm	129 lpm	159 lpm	182 lpm					
1" LFN170-M3	<sup>3</sup> / <sub>4</sub> x 1"	4 gpm	9.54	21 gpm	30 gpm	43 gpm	52 gpm	64 gpm	74 gpm					
CSUT		15 lpm	9.04	79 lpm	114 lpm	163 lpm	197 lpm	242 lpm	280 lpm					
1 <sup>1</sup> /4" LFN170-M3	1 <sup>1</sup> /4 x 1 <sup>1</sup> /4"	4 gpm	13.42	30 gpm	42 gpm	60 gpm	74 gpm	90 gpm	104 gpm					
CSUT		15 lpm	13.42	114 lpm	159 lpm	227 lpm	280 lpm	341 lpm	394 lpm					
11/2" LFN170-M3	1 <sup>1</sup> / <sub>4</sub> x 1 <sup>1</sup> / <sub>2</sub> "	5 gpm	14.90	33 gpm	47 gpm	67 gpm	82 gpm	100 gpm	115 gpm					
CSUT	1'/4 X 1'/2	19 lpm	14.90	125 lpm	128 lpm	254 lpm	310 lpm	379 lpm	435 lpm					
2" LFN170-M3	1 <sup>1</sup> /4 x 2"	7 gpm	17.89	40 gpm	57 gpm	80 gpm	98 gpm	120 gpm	139 gpm					
CSUT	1 '/4 X Z	26 lpm	17.09	151 lpm	216 lpm	303 lpm	371 lpm	454 lpm	526 lpm					



	BODY	CHECK	BODY																	
MODEL	INLETS	STOP	OUTLET						I	DIMENSIONS									WEI	GHT
	NPT	INLETS	NPT	A		B C		D E		F	F G			н		J				
		NPT		in. mm	in.	тт	in. mm	in.	тт	in. mm	in.	тт	in.	тт	in.	тт	in.	тт	lbs.	kgs
3/4 LFN170-M3	3⁄4	N/A	3⁄4	N/A	41/2	114	N/A	31⁄2	89	N/A	17/16	36	35/8	92	47⁄8	124	<b>2</b> <sup>15</sup> /16	75	4.8	2.2
3/4 LFN170-M3 CSUT	N/A	3⁄4	3⁄4	9¼ 235	41/2	114	11 <sup>7</sup> ⁄16 291	31⁄2	89	<b>1</b> <sup>13</sup> ⁄16 <b>46</b>	<b>1</b> <sup>7</sup> /16	36	35⁄8	92	41/8	124	<b>2</b> <sup>15</sup> /16	75	9.8	4.5
1 LFN170-M3	1	N/A	1	N/A	4%16	116	N/A	31⁄2	89	N/A	<b>1</b> <sup>7</sup> /16	36	35⁄8	92	41/8	124	<b>2</b> <sup>15</sup> /16	75	4.8	2.2
1 LFN170-M3 CSUT	N/A	3⁄4	1	101/8 264	4%16	116	121/16 319	31⁄2	89	<b>1</b> <sup>13</sup> ⁄16 <b>46</b>	<b>1</b> 7⁄16	36	35/8	92	47⁄8	124	<b>2</b> <sup>15</sup> /16	75	10.3	4.9
1¼ LFN170-M3	11⁄4	N/A	11⁄4	N/A	61/16	154	N/A	37/16	87	N/A	13⁄4	44	<b>31</b> <sup>11</sup> / <sub>16</sub>	94	51⁄4	133	41⁄2	114	9.4	4.3
11/4 LFN170-M3 CSUT	N/A	11⁄4	11⁄4	121/16 306	<b>6</b> <sup>1</sup> /16	154	15 <sup>1</sup> /16 383	37/16	87	<b>2</b> ½ 64	13⁄4	44	<b>31</b> <sup>11</sup> / <sub>16</sub>	94	51⁄4	133	<b>4</b> ½	114	19.3	8.8
11/2 LFN170-M3	11/2	N/A	1½	N/A	<b>6</b> <sup>1</sup> /16	154	N/A	37/16	87	N/A	13⁄4	44	<b>31</b> <sup>11</sup> / <sub>16</sub>	94	51⁄4	133	<b>4</b> ½	114	9.1	4.1
11/2 LFN170-M3 CSUT	N/A	11⁄4	1½	131⁄4 337	61/16	154	16¼ 413	37/16	87	<b>2</b> ½ 64	1¾	44	<b>31</b> <sup>11</sup> / <sub>16</sub>	94	5¼	133	<b>4</b> ½	114	19.8	9.0
2 LFN170-M3	2 (Hot) 11/2 (Cold)	N/A	2	N/A	67/16	164	N/A	<b>3</b> <sup>3</sup> ⁄16	81	N/A	<b>2<sup>1</sup>/</b> 16	52	31/8	98	53%	137	<b>4</b> ½	114	10.4	4.7
2 LFN170-M3 CSUT	N/A	11⁄4	2	13¾ 349	67/16	164	16¾ 425	<b>3</b> <sup>3</sup> ⁄16	81	<b>2</b> <sup>1</sup> / <sub>2</sub> <b>6</b> 4	<b>2<sup>1</sup>/</b> 16	52	31/8	98	53%	137	<b>4</b> ½	114	21.3	9.7

# **Typical Specification**

Master mixing valve shall feature paraffin-based, thermal actuation technology for precise temperature control. Valve shall be listed to ASSE 1017 and cUPC and shall be approved to ASSE 1017 & CSA B125.3 standards. Master mixing valve shall have an approach temperature of 5°F (3°C). Valve shall have an outlet temperature range from 90 – 180°F (32 to 82°C) with a lockable temperature-setting feature. Valve shall be manufactured of corrosion resistant materials and feature a single-seat design for positive shutoff. It shall have a Lead Free\* brass body.



constructed using Lead Free\* brass. Lead Free\* master mixing valves shall comply with state codes and standards, where applicable, requiring reduced lead content. Minimum flows to ASSE 1017 shall be  $^{3}/_{4}$  LFN170-M3 (3.0 gpm, 11 lpm), 1 LFN170-M3 (4.0 gpm, 15 lpm), 1 $^{1}/_{2}$  LFN170-M3 (5.0 gpm, 19 lpm), 2 LFN170-M3 (7.0 gpm, 26 lpm). Master mixing valves shall be of Watts Series LFN170-M3. Any alternate must have a written approval prior to bidding.