

For Agricultural and Industrial Applications

Job Name _____

Contractor _____

Job Location _____

Approval _____

Engineer _____

Contractor's P.O. No. _____

Approval _____

Representative _____

ANKA® AFU Series

Female Pipe Unions

Sizes: ¾" – 2" (20 – 50mm)

These pipe unions are made from the high grade glass reinforced nylon and are designed so they can be used in place of traditional metal fittings, with the advantage of being non-corrosive.

Features

- Can be taken apart for servicing
- Maximum pressure of 230 psi (1600 kPa)
- Strong Design
- Full Flow
- Non-Corrosive; using high quality materials

Applications

- Pumping
- Irrigation
- Plumbing
- Marine
- Industry
- Agriculture

Models

AFU34 US — ¾" (20mm)

AFU1 US — 1" (25mm)

AFU114 US — 1¼" (32mm)

AFU112 US — 1½" (40mm)

AFU2 US — 2" (50mm)



Materials

Body: Glass Fiber Reinforced Nylon

O Ring : Nitrile Rubber

Threads: NPT threads

Maximum Working

Pressure: 230 psi (1600 kPa) (16 bar)
@ 20°C

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



USA: T: (978) 689-6066 • F: (978) 975-8350 • Watts.com

Canada: T: (905) 332-4090 • F: (905) 332-7068 • Watts.ca

Latin America: T: (52) 81-1001-8600 • Watts.com