

**For Commercial Applications**

Job Name \_\_\_\_\_  
 Job Location \_\_\_\_\_  
 Engineer \_\_\_\_\_  
 Approval \_\_\_\_\_

Contractor \_\_\_\_\_  
 Approval \_\_\_\_\_  
 Contractor's P.O. No. \_\_\_\_\_  
 Representative \_\_\_\_\_

**LEAD FREE\***

**Model PWROKC4**  
**Kwik-Change™**  
**Reverse Osmosis (RO) Systems**

**Flow Rate: Up to 60 gallons per day (227 lpd)**

The Kwik-Change™ Reverse Osmosis (RO) System produces up to 60 gallons per day of high-quality water that exceeds the quality of most bottled waters.

**Features**

- Kwik-Change™ cartridges are the fastest changeable cartridges on the market
- ¼-turn Pivot filter makes for ease of accessibility and filter change, reduces the amount of tube connections for greater reliability and less potential leaks
- Proprietary cartridges connect to (and disconnect from) the unit by a simple ¼ turn
- Space saving design installs under sink or in limited space
- Adapt-A-Valve™ easily connects to water source for ¾" compression or ½" NPT
- Automatic shutoff – No need to shutoff incoming supply when changing filters
- Top mount designer faucet installs top side and provides a ¾" high-flow water delivery system
- Air Gap faucet meets local plumbing codes
- 3-Gallon water storage holding tank
- Additional faucet finishes available

**Performance**

Removes harmful contaminants including:

- Arsenic
- Barium
- Cadmium
- Chromium (Hexavalent)
- Chromium (Trivalent)
- Copper
- Cysts
- Cryptosporidium
- Entamoeba
- Flouride
- Giardia
- Lead
- Nitrate
- Nitrite
- Perchlorate
- Radium 226/228
- TDS (Total Dissolved Solids)
- Turbidity
- Toxoplasma

\*The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.



**PWROKC4**

**System Specifications**

Temperature: Minimum 40°F (4.4°C),  
 Maximum 100°F (37.8°C)  
 Pressure: Minimum 40psi (2.80 kg/cm2)  
 Maximum 85psi (6 kg/cm2)  
 pH: Minimum 2, Maximum 11  
 Iron (Fe): N/A Max 1.0 ppm  
 TDS (Total Dissolved Solids): N/A Max 1800 ppm  
 Hardness: N/A Max <1 grain  
 Unit Dimensions: Approx. 12" W x 15" H x 4" D

**Replacement Filter Pack**

MODEL	FREQUENCY	DESCRIPTION
PWFPK2KC4	6 Months	Includes sediment and pre-carbon filters only
PWFPK4KC4		Includes all filters and membrane
PWMEMKC60	2 - 5 years	60 gallon per day membrane
PWKCGAC13	Annually	GAC final filter

**Note:** Water conditions may require more frequent cartridge replacement

**Note:** Do not use with water that is microbiologically unsafe or of unknown quality without adequate disinfection before or after the system. Systems certified for cyst reduction may be used on disinfected waters that may contain filterable cysts.



System tested and certified by WQA against NSF/ANSI Standard 372 for "lead free" compliance

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.





---

**USA:** T: (800) 224-1299 • F: (978) 794-1848 • [Watts.com/PureWater](http://Watts.com/PureWater)  
**Canada:** T: (905) 332-4090 • F: (905) 332-7068 • [Watts.ca/PureWater](http://Watts.ca/PureWater)  
**Latin America:** T: (52) 81-1001-8600 • [Watts.com/PureWater](http://Watts.com/PureWater)