

For Residential and Commercial Applications

Job Name _____

Contractor _____

Job Location _____

Approval _____

Engineer _____

Contractor's P.O. No. _____

Approval _____

Representative _____

LEAD FREE*

Series LFFBV-4B, LFFBVS-4B

2-Piece, Full Port, Brass Ball Valves

Sizes: ¼" – 3"

Series LFFBV-4B, LFFBVS-4B 2-Piece, Full Port, Brass Ball Valves are suitable for a full range of liquids and gases in residential and commercial applications.

These valves feature an adjustable packing for longer service life, a bottom loaded blow-out proof stem for safety, a fluorocarbon elastomer stem O-ring to prevent stem leaking at installation, and are rated to 600psi WOG/150psi WSP ¼"– 3".

Features

- CSA approved threaded valves only ¼" – 3"
- Certified to NSF/ANSI Standard 61/8
- Metal-to-metal adapter body seal to eliminate adapter leaks after soldering
- Adjustable stem packing gland provides longer service life
- Bottom loaded blowout proof stem
- PTFE stem packing seal and seats
- Machined chrome plated Lead Free brass ball for sizes ¼" - 1" and stainless steel for sizes 1¼" - 3"
- Complies with MSS-SP-110


Models

LFFBV-4B ¼" – 3" threaded end connections

LFFBVS-4B ½" – 3" solder end connections*

Specifications

Approved valves shall be 2-piece full port design constructed of a forged Lead Free brass body and end adapter. Seats and stem packing shall be PTFE. Stem to be bottom-loaded, blow-out proof design with a fluorocarbon elastomer O-ring to prevent stem leakage. Valves required to have an adjustable packing gland and ½" - 1" chromed plated Lead Free brass ball and stainless steel for 1¼" - 3". Threaded valves ¼" – 2" shall be CSA approved to ½ psig and 5 psig and certified to NSF/ANSI Standard 61/8. Solder valves also required to be certified to NSF/ANSI Standard 61/8. Valve sizes ¼" – 2" pressure rated to 600 psi WOG and 150 psi WSP. Sizes 2½" - 3" pressure rated to 400 psi WOG and 125psi WSP. Valves specified are Watts Series LFFBV-4B or LFFBVS-4B.



Approvals

¼" – 3" FBV-4

½" – 3" FBVS-4

Certified to NSF/ANSI Standard 61/8



Gas Approvals (Threaded Valves Only)

¼" – 2"

CSA

½ psig, 5 psig

@ -40°F to 125°F



Pressure — Temperature

Temperature Range: -40°F to 400°F (-40°C to 204°C)

Pressure Rating: ¼" – 3"
600psi (41.4 bar) WOG non-shock
150psi (10.3 bar) WSP
2½" – 3"
400psi (27) WOG non-shock
125psi WSP

Installation Information

Apply heat with the flame directed **AWAY** from the center of the valve body. Excessive heat can harm the seats. After soldering, the packing nut may have to be tightened.

*This valve is designed to be soft soldered into lines without disassembly, using a low temperature solder to 420°F (216°C). Higher temperature solders may damage the seat material.

NOTICE


The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

NOTICE

Inquire with governing authorities for local installation requirements


*The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.

Materials



- A Handle Nut** Zinc plated carbon steel
- B Handle Assembly** Zinc plated carbon steel with vinyl insulator
- C Packing Nut** Brass
- D Stem Packing** Virgin PTFE
- E O-Ring** EPDM
- G Stem** Lead Free brass
- H Tag** Cardboard, Mylar coated both sides
- I Body** Forged Lead Free brass
- J Seats** Virgin PTFE
- K Ball** Lead Free brass (¼" - 1") Stainless steel (1¼" - 3")
- L Adaptor** Forged brass

Dimensions-Weights



SIZE		DIMENSIONS									
	C		H		I		L		L1		
in.	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	
¼	1 ¹³ / ₁₆	46	3 ⁷ / ₁₆	87	7 ¹ / ₁₆	11	1¾	45	—	—	
⅜	1 ¹³ / ₁₆	46	3 ⁷ / ₁₆	87	½	13	1¾	45	—	—	
½	1¾	36	3	78	½	13	2	52	1 ⁷ / ₈	50	
¾	1½	39	4 ¹ / ₈	105	1 ¹ / ₁₆	18	2 ⁵ / ₁₆	59	1 ¹³ / ₁₆	69	
1	1 ¹³ / ₁₆	45	4 ³ / ₁₆	105	1 ⁵ / ₁₆	24	2 ¹³ / ₁₆	71	3 ³ / ₁₆	83	
1¼	1 ⁷ / ₈	50	4 ¹⁵ / ₁₆	125	1 ³ / ₁₆	30.5	3 ³ / ₁₆	80	3 ³ / ₁₆	92	
1½	2½	63	4 ¹⁵ / ₁₆	125	1¾	37	3½	89	4 ⁵ / ₁₆	109	
2	2 ¹¹ / ₁₆	68	7	180	1 ⁷ / ₈	49.5	4 ³ / ₁₆	107	5 ⁵ / ₁₆	136	
2½	4¾	118	9¾	240	2 ⁵ / ₈	67	5 ⁵ / ₈	141	6½	164	
3	5	128	9¾	240	3 ¹ / ₈	79.5	6 ³ / ₈	162	7½	191	



USA: T: (978) 689-6066 • F: (978) 975-8350 • Watts.com
 Canada: T: (905) 332-4090 • F: (905) 332-7068 • Watts.ca
 Latin America: T: (62) 81-1001-8600 • Watts.com