For Health Hazard Applications

Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No.
Approval	Representative

LEAD FREE*

Series LFNLF9

Dual Check Vacuum Breakers for Laboratory Faucets

Sizes: 3/8"

Series LFNLF9 Dual Check Vacuum Breakers for Laboratory Faucets are used for noncontinuous pressure, health hazard, applications and are backsiphonage backflow preventers. This series is specially made for laboratory faucets where portable hoses can be attached and prevent the flow of contaminated water back into the potable water supply. These vacuum breakers can be installed on new or existing faucets without plumbing changes. The LFNLF9 features Lead Free* construction to comply with Lead Free* installation requirements.

Pressure-Temperature

Temperature Range: 33°F - 180°F (0.5°C - 82°C) Maximum Working Pressure: 150psi (10.3 bar)

Applications

LFNLF9 should be installed on every laboratory outlet where a hose can be attached. Its unique design provides full protection against all backsiphonage conditions.


To prevent tampering, it is recommended that the LFNLF9 be secured to the laboratory faucet with Loctite.

Use LFNLF9 for non-continuous pressure applications.



LFNLF9

Laboratory Faucet



NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

NOTICE

Inquire with governing authorities for local installation requirements

*The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.



Construction

LFNLF9 is suitable for either hot or cold water service. It features brass construction and a primary check valve utilizing a soft disc which seats against a soft rubber mating part to ensure tight closing. A secondary check valve utilizes a soft disc-to-metal seating. LFNLF9 provides better-than-average flow rate and consequently lower pressure loss. Construction is brass body with polished chrome plating, stainless steel working parts and durable rubber diaphragm and disc.

Standards

CSA B64.7 ASSE 1035 - "Laboratory Faucet Vacuum Breakers"


Approvals












Dimensions - Weights

SIZE	DIMENSIONS					WEIGHT		
·	l A	A B		B ₁				
in.	in.	mm	in.	mm	in.	mm	lbs.	kgs
3/8	23/8	60	11/4	32	1	25	.38	.17

Capacity





ES-LFNLF9 1322 © 2013 Watts