




Standard Materials

- Body & Cover: 304L Stainless Steel (standard)
316L Stainless Steel
- Flanges: Class D Zinc Plated Steel with
Stainless Steel Seal Welds (standard)
304L Stainless Steel (-09 Option)
- Trim: 316 Stainless Steel
- Elastomers: Buna-N (standard)
EPDM
Viton
- Stem, Nut & Spring: Stainless Steel



Dimensions

	A	B	C	D	E	F	G	H	I	
VALVE SIZE	GLOBE 150#	GLOBE 300#	COVER TO CENTER	ANGLE 150#	ANGLE 300#	ANGLE 150 #	ANGLE 300#	PORT SIZE	PORT SIZE	SHIPPING WEIGHTS*
4	15	15-5/8	10-5/8	7-1/2	7-7/8	5	5-5/16	1/2	3/4	77
6	20	21	13-3/8	10	10-1/2	6	6-1/2	1/2	3/4	168
8	25-3/8	26-3/8	16	12-3/4	13-1/4	8	8-1/2	1	1	225
10	29-3/4	31-1/8	17-1/8	14-7/8	15-9/16	8-5/8	9-5/16	1	1-1/4	376
12	34	35-1/2	20-7/8	17	17-3/4	13-3/4	14-1/2	1	1-1/4	450
16	41-3/8	43-1/2	25	20-13/16	21-5/8	15-11/16	16-1/2	1	1-1/2	850

*Estimated in lbs.

Description

The AMES Models 600GS and 600AS are reduced port, dual chamber basic valves that incorporate a one-piece disc and diaphragm assembly. This assembly is the only moving part within the valve, allowing it to open or close as commanded by the pilot control system.

When pressure is applied to the upper diaphragm chamber and released from the lower diaphragm chamber, the valve travels to a closed position. When pressure is applied to the lower diaphragm chamber and released from the upper diaphragm chamber the valve travels to a full open position. When pressure is balanced between the upper and lower diaphragm chambers, the valve will hold an intermediate position until commanded to modulate open or closed by the pilot control system.

The Stainless Steel design offers superior corrosion resistance, as well as a lightweight alternative to conventional heavy iron valves. Stainless Steel construction provides extended, diaphragm life and reduces the frequency and labor costs associated with traditional maintenance repairs.

- Model 600GS: Globe Pattern Dual Chamber Basic Valve
- Model 600AS: Angle Pattern Dual Chamber Basic Valve

Operating Pressure

150 Flanged = 250 psi / 300 Flanged = 400 psi

Operating Temperature

- Buna-N: 160°F Maximum
- EPDM: 300°F Maximum

Flow Data - 600GS (Globe) / 600AS (Angle)

Valve Size - Inches	4	6	8	10	12	16
Maximum Continuous Flow Rate Gpm (Water)	800	1850	3100	5000	7000	11100
Maximum Intermittent Flow Rate Gpm (Water)	1000	2300	4000	6250	8900	14100
C _v Factor GPM (Globe)	210	460	790	1260	1725	2940
C _v Factor GPM (Angle)	237	534				

Estimated

Maximum continuous flow based on velocity of 20 ft. per second.

Maximum intermittent flow based on velocity of 25 ft. per second.


The C_v Factor of a valve is the flow rate in US GPM at 60° F that will cause a 1 psi drop in pressure.

The factors stated are based upon a fully open valve.

Cv factor can be used in the following equations to determine Flow (Q) and Pressure Drop (Δ P):

$$Q (\text{Flow}) = C_v \sqrt{\Delta P} \quad \Delta P (\text{Pressure Drop}) = (Q/C_v)^2$$

Headloss



Valve Cover Chamber Capacity

Valve Size (in)	4	6	8	10	12	16
fl.oz.	22	70				
U.S. Gal			1-1/4	2-1/2	4	9-1/2

Valve Travel

Valve Size (in)	4	6	8	10	12	16
Travel (in)	1	1-1/2	2	2-1/2	3	4