

BASIC VALVES

Globe

900GS (Globe) 900AS (Angle)

Angle

0106

Standard Materials

Body & 304L Stainless Steel (standard)

Cover: 316L Stainless Steel

Flanges: Class D Zinc Plated Steel with

Stainless Steel Seal Welds (standard) 304L Stainless Steel (-09 Option)

Trim: 316 Stainless Steel

Elastomers: Buna-N (standard)

EPDM Viton

Stem, Nut Stainless Steel

& Spring:

C H H D D E E

Dimensions

	А	В	С	D	E	F	G	Н	I	J	
VALVE	GLOBE	GLOBE	COVER TO	ANGLE	ANGLE	ANGLE	ANGLE	PORT	PORT	PORT	SHIPPING
SIZE	150#	300#	CENTER	150#	300#	150#	300#	SIZE	SIZE	SIZE	WEIGHTS*
4	15	15-5/8	14-1/4	7-1/2	7-7/8	5	5-5/16	1/2	3/4	1/2	87
6	20	21	18-7/16	10	10-1/2	6	6-1/2	1/2	3/4	1/2	178
8	25-3/8	26-3/8	21-13/16	12-3/4	13-1/4	8	8-1/2	1	1	1/2	240
10	29-3/4	31-1/8	23-3/8	14-7/8	15-9/16	8-5/8	9-5/16	1	1-1/4	1/2	397
12	34	35-1/2	29-5/16	17	17-3/4	13-3/4	14-1/2	1	1-1/4	1/2	480
16	41-3/8	43-1/2	35	20-13/16	21-5/8	15-11/16	16-1/2	1	1-1/2	1/2	925

*Estimated in lbs.

Description

The AMES Models 900GS and 900AS are full port, dual chamber basic valves that incorporate a one-piece disc and diaphragm assembly. This assembly is the only moving part within the valve, allowing it to open or close as commanded by the pilot control system.

When pressure is applied to the upper diaphragm chamber and released from the lower diaphragm chamber, the valve travels to a closed position. When pressure is applied to the lower diaphragm chamber and released from the upper diaphragm chamber the valve travels to a full open position. When pressure is balanced between the upper and lower diaphragm chambers, the valve will hold an intermediate position until commanded to modulate open or closed by the pilot control system.

The Stainless Steel design offers superior corrosion resistance, as well as a lightweight alternative to conventional heavy iron valves. Stainless Steel construction provides extended, diaphragm life and reduces the frequency and labor costs associated with traditional maintenance repairs.

Model 900GS: Globe Pattern Dual Chamber Basic Valve Model 900AS: Angle Pattern Dual Chamber Basic Valve

Operating Pressure

150 Flanged = 250 psi / 300 Flanged = 400 psi

Operating Temperature

Buna-N: 160°F Maximum EPDM: 300°F Maximum Viton: 250°F Maximum

Flow Data - 900GS (Globe) / 900AS (Angle)

Valve Size - Inches	4	6	8	10	12	16
Maximum Continuous Flow Rate Gpm (Water)	800	1850	3100	5000	7000	11100
Maximum Intermittent Flow Rate Gpm (Water)	1000	2300	4000	6250	8900	14100
C _v Factor GPM (Globe)	210	460	790	1260	1725	2940
C _v Factor GPM (Angle)	250	561	990	1590	2500	4200

Estimated

Maximum continuous flow based on velocity of 20 ft. per second.

Maximum intermittent flow based on velocity of 25 ft. per second.


The C_v Factor of a value is the flow rate in US GPM at 60° F that will cause a 1 psi drop in pressure.

The factors stated are based upon a fully open valve.

Cv factor can be used in the following equations to determine Flow (Q) and Pressure Drop (\triangle P):

Q (Flow) =
$$C_v \sqrt{\Delta P}$$
 ΔP (Pressure Drop) = $(Q/C_v)^2$

Headloss



Valve Cover Chamber Capacity

Valve Size (in)	4	6	8	10	12	16
fl.oz.	22	70				
U.S. Gal			1-1/4	2-1/2	4	9-1/2

Valve Travel

 Tarre Have									
Valve Size (in)	4	6	8	10	12	16			
Travel (in)	1	1-1/2	2	2-1/2	3	4			