



PUMP CONTROL VALVE WITH PRESSURE REDUCING FEATURE

03/06

980 Series

—Model— **981-09**
681-09

Specifications

The Pump Control Valve with Pressure Reducing Feature shall be a pilot operated diaphragm valve designed to minimize the surges associated with the starting and stopping of pumps, and automatically reduce pump outlet pressure to a constant lower downstream pressure regardless of varying flow rates. The valve shall be designed to open at an adjustable rate upon pump start-up, and close at an adjustable rate upon pump shut-off. When the valve is near closed the limit switch shall be tripped, turning the pump off. The pump shall start and stop against a closed valve. The valve shall have provisions for manual operation in the event of power outage. Solenoid voltage shall be _____ and enclosure shall be NEMA 4 General Purpose.

The main valve shall be a hydraulically operated, single diaphragm actuated, globe or angle pattern valve. Y-pattern valves shall not be permitted. The valve shall contain a disc and diaphragm assembly that forms a sealed chamber below the valve cover, separating operating pressure from line pressure. The diaphragm shall be constructed of nylon reinforced Buna-N, and shall not seal directly against the valve seat and shall be fully supported by the valve body and cover. Rolling diaphragm construction will not be allowed and there shall be no pistons operating the main valve or any pilot controls.

The main valve body, cover, flanges, and all internal components shall be fabricated 304L Stainless Steel. The main valve trim and throttling components (cover bearing, valve seat and disc guide) shall be Stainless Steel.

The disc and diaphragm assembly shall contain a Buna-N synthetic rubber disc with a rectangular cross-section that is securely retained on 3-1/2 sides by a disc retainer and disc guide. Diaphragm assemblies utilizing bolts or cap screws for component retention will not be permitted.

The exposed portion of the seat disc shall contact the valve seat and seal drip-tight. The disc and diaphragm assembly must be guided by two separate bearings, one installed in the valve cover and one concentrically located within the valve seat, to avoid deflection and assure positive disc-to-seat contact. Center guided valves will not be permitted. All necessary repairs shall be made from the top of the valve while the body remains in line.

The pilot control system shall contain a 3-Way Solenoid Pilot with screw type Manual Operator, Single Limit Switch, 3-Way Accelerator Pilot with integral orifice, Pressure Reducing Pilot, separate Adjustable Opening and Closing Speed Controls, (2) Check Valves, an external Y-Strainer and Isolation Ball Valves on all body connections. The pilot control system shall utilize stainless steel tubing and fittings, and all pilot control system components including valve accessories shall be stainless steel. The adjustment range of the pressure reducing pilot shall be 30-300 psi.

The valve shall be AMES Model 981GS-09 / 681GS-09 (Globe) or 981AS-09 / 681AS-09 (Angle) Pump Control Valve with Pressure Reducing Feature.