



# PRESSURE REDUCING AND SUSTAINING CONTROL VALVE WITH SURGE CONTROL FEATURE

03/06

## 910 Series

—Model— **912-09-11**  
**612-09-11**

### Specifications

The Pressure Reducing and Sustaining Control Valve with Downstream Surge Control Feature shall be a pilot operated diaphragm valve designed to automatically reduce a fluctuating higher upstream pressure to a constant lower downstream pressure regardless of varying flow rates, sustain a minimum upstream pressure, and quickly modulate toward a closed position when a sudden high pressure downstream condition occurs.

The main valve shall be a hydraulically operated, single diaphragm actuated, globe or angle pattern valve. Y-pattern valves shall not be permitted. The valve shall contain a disc and diaphragm assembly that forms a sealed chamber below the valve cover, separating operating pressure from line pressure. The diaphragm shall be constructed of nylon reinforced Buna-N, and shall not seal directly against the valve seat and shall be fully supported by the valve body and cover. Rolling diaphragm construction will not be allowed and there shall be no pistons operating the main valve or any pilot controls.

The main valve body, cover, flanges, and all internal components shall be fabricated 304L Stainless Steel. The main valve trim and throttling components (cover bearing, valve seat and disc guide) shall be Stainless Steel.

The disc and diaphragm assembly shall contain a Buna-N synthetic rubber disc with a rectangular cross-section that is securely retained on 3-1/2 sides by a disc retainer and disc guide. Diaphragm assemblies utilizing bolts or cap screws for component retention will not be permitted.

The exposed portion of the seat disc shall contact the valve seat and seal drip-tight. The disc and diaphragm assembly must be guided by two separate bearings, one installed in the valve cover and one concentrically located within the valve seat, to avoid deflection and assure positive disc-to-seat contact. Center guided valves will not be permitted. All necessary repairs shall be made from the top of the valve while the body remains in line.

Pilot control systems for valves 3" and smaller shall contain a Flow Clean Strainer, Fixed Orifice Closing Speed, Adjustable Opening Speed Control, Downstream Surge Control Pilot, Pressure Sustaining Pilot and Pressure Reducing Pilot. Pilot control systems for valves 4" and larger shall contain an external Y-Strainer, Fixed Orifice Closing Speed, Downstream Surge Control Pilot, Pressure Sustaining Pilot, Pressure Reducing Pilot and Isolation Ball Valves on all body connections. All pilot control systems shall utilize stainless steel tubing and fittings regardless of valve size, and all pilot control system components including valve accessories shall be stainless steel. The adjustment range of the pressure sustaining pilot and the downstream surge control pilot shall be 20-200 psi and the pressure reducing pilot shall be 30-300 psi.

The valve shall be AMES Model 912GS-09-11 or 612GS-09-11 (globe) or 912AS-09-11 or 610AS-09-11 (angle) pattern Pressure Reducing and Sustaining Control Valve with Downstream Surge Control Feature.