




ONE-WAY FLOW ALTITUDE VALVE with PRESSURE SUSTAINING FEATURE

03/06

960 Series

—Model— **962**
662

- Designed for Tank Fill applications
- Opens when Tank head pressure is below setpoint
- Closes when Tank head pressure is above setpoint
- Throttles to maintain minimum upstream pressure
- Tank Sense Line is field installed (to Tank or standpipe)
- Adjustable Opening and Closing Speed
- Altitude and Sustaining setpoints are adjustable



STANDARD COMPONENTS

- | | |
|----------------------------------|------------------------------|
| 1 - Main Valve (Single Chamber) | 6 - Adjustable Closing Speed |
| 2 - Model 22 Accelerator Control | 7 - Adjustable Opening Speed |
| 3 - Altitude Control | P - Position Indicator |
| 4 - Check Valve | |
| 5 - Pressure Sustaining Control | |

OPTIONS and ACCESSORIES

- X - Isolation Cocks
- FC - Flo-Clean Strainer
- Y - Y-Strainer (Replaces Flo-Clean)
- L - Limit Switch