


Provides Unsurpassed Protection from Temperature & Pressure

Series e700 Combination T/P Valve



POWERS™
A **WATTS** Brand

PowersControls.com



Features and Benefits

- Provides the thermal protection of a thermostatic valve not found with common pressure balance valves, while also responding almost instantaneously to a dramatic pressure fluctuation...even up to 50%.
- Unlike common pressure balance valves, it does not require the seasonal adjustment of the limit stop.
- Affordable. Will never be value-engineered.
- 5-year limited warranty on internal tempering mechanism.
- Capable of providing mixed outlet temperature within 10°F of hot water supply temperature for applications where low hot water temperatures exist.
- Won't stick or seize due to harsh water conditions.
- Listed to the performance requirements of ASSE 1016 T/P and IAPMO cUPC.
- Self-contained cartridge simplifies maintenance and repair. Installs in 5 minutes.
- Back-to-back installation without costly cross-over piping by simply rotating the stem 180° re-labeling the ports.

Advanced Thermal Actuation (ATA) Technology dramatically improves Valve performance and safety for the user while lowering the risk of liability for the facility owner

POWERS™
A WATTS Brand



Safety for Your Healthcare Facility

Healthcare & Bather Safety

The market for America's aging population is growing rapidly. As the baby boomer generation draws closer to retirement, robust growth will continue well into the future. By 2025, America will experience a 68% increase for those in the 55 – 64 age group and a 75% increase for those in the 65+ age group. In 2025, those at the traditional retirement age of 65 will account for 20% of the country's population, up from the current 13.4%.

The elderly, whose physiological, mental and emotional capacities diminish over time and those who require assistance from caregivers, are at a higher risk for scalding. HydroGuard T/P provides the utmost level of safety by protecting against severe temperature and pressure changes.




Table 1 - Population ages 65 Years and Over: 1985-2050
(Source: US Census Bureau)

BATH SHOWER SYSTEMS



e700 complete upgrade kits
220 451 (top), 220 452 (bottom), and
220 453 (not shown)



*additional shower system configuration shown on PS_CompUnits_e700


Bacteria/Legionella Protection

Is Lower Better? The Other Side to the Coin

It's truly a double-edged sword. Lowering hot water supply temperature can minimize the risk of scalding to the bather but at the same time creates other potential health concerns. Among the most significant is the growth and proliferation of bacteria within the plumbing system, more specifically legionella.


Many healthcare professionals are convinced the occurrence of legionella is rare, when in fact the disease is more commonplace. Of the 2.4 million cases of pneumonia each year, it is estimated that as many as 100,000 are cases of Legionnaire's disease, and as few as 1,000 cases are actually reported to the CDC (U.S. Center for Disease Control and Prevention).

OSHA's technical manual on legionnaire's disease states that water should be stored at a minimum of 140°F and delivered to all outlets at a minimum of 122°F to "minimize the growth of legionellae in a system". At 140°F, legionellae are killed within 32 minutes, at 151°F legionellae die within 2 minutes.



Affordable T/P Technology

Minimize Bacteria Risk, Protect Against Scalding



Valve Type	Protection Provided per ASSE 1016*		Price & Performance Value
Point-of-use	Hot water temperature increases +25°F	Supply pressure fluctuations up to 50%	Complete Protection and Affordability
- Type P - Pressure balance	NO	YES	NO
- Type T - Thermostatic	YES	NO	NO
- Type T/P** - Combination	YES	YES	YES
	HydroGuard T/P	HydroGuard T/P	HydroGuard T/P

*holds ±3°F

Generate hot water at 140°F*+ → Distribute at 122°F*+ → Protect bather with T/P technology

- **T/P -
- Provides temperature and pressure control at the point-of-use
- Provides temperature protection against seasonal changes in cold water temperature
- Prevents thermal shock resulting from sudden and dramatic changes in supply temperature and pressure
- Provides redundant temperature protection in the event of an upstream failure

HydroGuard® T/P

Temperature Effects


Type P valves come with a limit stop that sets the handle rotation to the maximum hot water position. The limit stop should be adjusted regularly by a certified plumber to accommodate for variations in seasonal cold water temperature especially in regional areas where extreme weather conditions dramatically affect temperature from water sources such as lakes and rivers. If the pressure balancing valve is installed during the winter months, the limit stop is usually set to deliver higher outlet temperature to compensate for colder conditions. As the weather gets warmer, temperature from cold water sources will rise causing an increase in water outlet temperature making it necessary to re-adjust the limit stop. Since temperature variation is brought about by seasonal changes, periodic adjustments to the limit stop becomes essential thereby ensuring the valve delivers safe water. Failure to regulate the limit stop in pressure balancing valves can cause higher water outlet temperature that can potentially be dangerous.

Effects of Seasonal Water Temperature Changes on Shower Valves

Hot Water Temperature at 140°F

**without adjustment of the limit stop*

**Exposure at 120°F for about 8 minutes may cause first degree burns*



CW TEMP	HW TEMP	Outlet TEMP. Type P	Outlet TEMP. Type T/P
40°	140°	115.0°	115.0°
50°	140°	117.5°	115.0°
60°	140°	120.0°	115.0°
70°	140°	122.5°	115.0°
80°	140°	125.0°	115.0°
		$\Delta +10.0^\circ$	0°

Type P: Outlet temperature increase between CW 40°F and 80°F = 10

Type T/P: Outlet temperature increase between CW 40°F and 80°F = 0

Combination valves (type T/P) eliminate the need for seasonal adjustment of the limit stop required by pressure balancing valves to accommodate variations in cold water inlet temperatures. They also protect against unauthorized adjustments. Unlike thermostatic valves (type T), combination valves must compensate for greater pressure fluctuations (50% vs 20%) within a plumbing system. The underlying reason that makes Type T/P superior is that the valves allow water to be distributed at higher temperatures (to inhibit legionella growth) while delivering safe temperatures to the bather (to protect from scalding).

Ordering Information

	Order Code								
Valves									
ABS Trim	e705								
Metal Trim	e710								
Flat Metal Trim	e707								
Showerheads									
Economizer, Chrome-Plated ABS, Adjustable.....	J								
Standard, Chrome-Plated Brass.....	K								
Deluxe, Chrome-Plated Brass	M								
Low Flow (1.5 gpm) Chrome Plated.....	G								
Low Flow (1.5 gpm) Chrome Plated.....	H								
Arm and Flange Kits									
Standard Arm and Flange	1								
Deluxe Arm and Flange.....	2								
Standard Arm/Flange & Hi-Temp. Shut-Off.....	4								
Deluxe Arm/Flange & Hi-Temp. Shut-Off	5								
Tub Spouts									
Diverter, Chrome-Plated Brass, 3/4" IPS	Q								
Non-Diverter, Chrome-Plated, 1/2" IPS	R								
Diverter, Chrome-Plated, 1/2" IPS.....	S								
Diverter, Chrome-Plated Brass, 1/2" IPS	T								
Diverter, Chrome-Plated, 1/2" Slipfit	U								
Hand Shower Systems									
24" Chrome ADA Wall Grab Bar System	1								
36" Chrome ADA Wall Grab Bar System	2								
Deluxe, Metal Hose, 30" Slide Bar.....	3								
Professional, Vinyl Hose, 30" Slide Bar.....	4								
Standard, Metal Hose, Two Wall Hooks	5								
Deluxe, Metal Hose, 24" Slide Bar.....	6								
Professional, Vinyl Hose, 24" Slide Bar.....	7								
Standard Plus, Metal Hose, 24" Slide Bar.....	8								
European, Metal Hose, 23" Slide Bar.....	9								
Low Flow (1.5 gpm), Metal Hose, Glide Rail.....	L								
Professional, Metal Hose, 30" Glide Rail.....	N								
Diverter									
Concealed Diverter Valve, 1/2" IPS.....	Y								
Exposed Diverter, Shower Arm-Type, Chrome-Plated	Z								
Diverter, Concealed, Deluxe ABS Handle	A								
Diverter, Concealed, Deluxe Metal Handle.....	B								
Vacuum Breakers									
Vacuum Breaker, Elevated, Chrome-Plated	V								
Vacuum Breaker, In-Line	W								

Specifications:

Construction	Cast Bronze
Capacity	4 gpm @ 45 psid 50/50 mix
Maximum Hot Water Supply Temperature	190°F (88°C)
Minimum Hot Water Supply Temperature (approach temperature)	10°F (5.5°C) above set point
Maximum Operating Pressure	125psig (862 kPa)
Maximum Static Pressure	125psig (862 kPa)
Minimum Flow tested to 1016 (for +/- 3°F performance)	1.0 gpm (3.781 L/min)
Shipping Weight	3.5 lbs (1.6 kg)

Typical Specifications:

Valve shall meet the performance requirements of ASSE 1016, Type T/P compensating for 50% fluctuation in supply line pressures and compensate for changes in the water supply temperatures. Valve shall be capable of supplying mixed water temperature within 10°F of hot water supply temperature. Valve shall contain a powerful, paraffin-based thermal actuator and feature a self-contained cartridge design for ease of repair and maintenance.

Water tempering valve shall not be subject to failure due to the lime build-up or dirt particles. Construction shall be conducive to long lasting, trouble free life, and shall not have close fitting, sliding parts, which through wear or binding, may impair operation.

Valve shall have all cast bronze housing and a capacity of 4 gpm at 45psid. Valve shall include an adjustable brass to brass limit stop, factory set at 110°F. Valve shall always open through cold water to maximize bather safety.

Valve shall be Powers # e7xx. Any alternates must have written approval prior to bidding.

POWERS™

A WATTS Brand

USA: T: (800) 669-5430 • F: (847) 229-0526 • PowersControls.com
 Canada: T: (905) 332-4090 • F: (905) 332-7068 • PowersControls.ca
 Latin America: T: (52) 81-1001-8600 • PowersControls.com