

Job Name \_\_\_\_\_

Contractor \_\_\_\_\_

Job Location \_\_\_\_\_

Approval \_\_\_\_\_

Engineer \_\_\_\_\_

Contractor's P.O. No. \_\_\_\_\_

Approval \_\_\_\_\_

Representative \_\_\_\_\_

# HydroGuard® XP Series

## Emergency Tempering Valve

### Supply Fixture with Cold Water Bypass

### Bottom Inlets/Bottom Outlet Exposed

#### Features

- Powers' Advanced Thermal Actuator provides precise temperature control
- Exclusive internal cold water bypass ensures cold water flow in the event of loss of hot water
- Flow effectively shuts down upon loss of cold water supply when tested under the condition specified in ASSE 1071 standard
- Vandal-resistant locking mechanism to secure temperature setting
- Factory tested
- Rough bronze and chrome finishes
- Checkstops to prevent cross flow

US Patent 6,575,377

Advanced  
Thermal Activation

#### Specifications

Connections	1/2" (15 mm) inlets and outlets
Maximum Operating Pressure	125psi (861 kPa)
Maximum Hot Water Temperature	180°F (82°C)
Temperature Adjustment Range	60 – 95°F (15 – 35°C)
Factory Set Temperature*	85°F (29°C)
Bypass flow rate at 30psid*	6.5 gpm (25 lpm)
Maximum flow with cold water shutoff*	0.5 gpm (1.9 lpm)
Listing—Valve Only	ASSE 1071 and IAPMO UPC

\*When tested under conditions specified in ASSE 1071 Standard

#### NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.


#### Capacity

Flow Capacity at 85°F (29.4°C)									
Pressure Drop Across Valve									
Model	Min. Flow to ASSE 1071	C <sub>v</sub>	5 psi (34 kPa)	10 psi (69 kPa)	15 psi (103 kPa)	20 psi (138 kPa)	30 psi (207 kPa)	45 psi (310 kPa)	60 psi (414 kPa)
ES150	1.0 gpm 3.8 lpm	1.59	3.6 gpm 13.6 lpm	5.0 gpm 18.9 lpm	6.2 gpm 23.5 lpm	7.1 gpm 26.9 lpm	8.7 gpm 32.9 lpm	10.7 gpm 40.5 lpm	12.3 gpm 46.6 lpm

Powers product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Powers Technical Service. Powers reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Powers products previously or subsequently sold.

**POWERS™**  
A WATTS Brand

Dimensions



Note:  
Dimensions are shown ±1/2"  
Dimensions in brackets are in mm

Ordering Information

Valve	Order Code	
8.7 gpm (32.9 lpm) @ 30 psi (207 kPa)	ES150	
<b>Finish</b>		
Rough Bronze	A	
Chrome Plated	B	
<b>Piping Inlets/Outlet</b>		
Bottom/Bottom	F	
<b>Cabinet Style</b>		
Stainless Steel, Recessed	N	
Painted, Recessed	R	
<b>Options</b>		
None	0	
T/P Gauge on Inlets	5	
<b>Alarm System</b>		
None	0	
AquaSentry® 2	4	

Recirculation Piping Diagram

Please see Piping Diagram Section of this catalog.

Typical Specification

Cabinet Supply Fixture for supplying tepid water to emergency fixtures shall be factory assembled, tested and include a stainless steel or painted steel cabinet. Thermostatic mixing valve must have internal cold-water bypass system to ensure flow in the event of valve failure or loss of hot water supply. Supply fixture also includes copper piping, ball valve(s) and temperature/pressure gauge for diagnostics. The valve shall be listed to ASSE 1071 and IAPMO UPC, provide precise temperature control over a wide range of flow conditions, and effectively shut down on loss of cold water. The valve shall feature paraffin-based actuation technology and checkstops to prevent cross flow. The valve shall be factory set to 85°F (29°C) with a lockable mean of securing the temperature.

The valve shall be Powers' model ES150 \_ \_ \_ \_ . All alternatives must have written approval prior to bidding.



USA: Tel: (800) 669-5430 • Fax: (847) 229-0526 • PowersControls.com  
Canada: Tel: (905) 332-4090 • Fax: (905) 332-7068 • PowersControls.ca  
Latin America: Tel: (52) 81-1001-8600 • PowersControls.com