Job Name	Contractor
	Approval
Job Location	Approval
Engineer	Contractor's P.O. No.
Approval	Representative

HydroGuard[®] XP Series Emergency Tempering

With Cold Water Bypass

Features

- Powers' Advanced Thermal Actuator provides precise temperature control
- Exclusive internal cold water bypass ensures cold water flow in the event of loss of hot water
- Flow effectively shuts down upon loss of cold water supply when tested under the condition specified in ASSE 1071 standard
- · Vandal-resistant locking mechanism to secure temperature setting
- · Factory tested
- · Rough bronze and chrome finishes
- Checkstops to prevent cross flow

US Patent 6,575,377

Specifications

Capacity

Flow Capacity at 85°F (29.4°C)									
Pressure Drop Across Valve									
Model	Min. Flow to	C	5 psi	10 psi	15 psi	20 psi	30 psi	45 psi	60 psi
Model	ASSE 1071	C _V	(34 kPa)	(69 kPa)	(103 kPa)	(138 kPa)	(207 kPa)	(310 kPa)	(414 kPa)
ES150	1.0 gpm	1.59	3.6 gpm	5.0 gpm	6.2 gpm	7.1 gpm	8.7 gpm	10.7 gpm	12.3 gpm
	3.8 lpm		13.6 lpm	18.9 lpm	23.5 lpm	26.9 lpm	32.9 lpm	40.5 lpm	46.6 lpm










Advanced Thermal Activation



^{*} When tested under conditions specified in ASSE 1071 Standard

Dimensions



Ordering Information

	E S 1 5 0	-				
Order Code						
<u>Finish</u>						
Rough Bronze	1					
Chrome Plated	2					
Temperature/Pressure Gauge on Outlet						
None	0					
For rough bronze	1					
or chrome plated	2					

Recirculating Piping Diagram

Please see Piping Diagram Section of the Powers Full Line Catalog.

Typical Specification

Thermostatic mixing valve for supplying tepid water to emergency fixtures shall feature internal cold-water bypass system to ensure flow in the event of valve failure or loss of hot water supply. The valve shall be listed to ASSE 1071 and IAPMO UPC provide precise temperature control over a wide range of flow conditions, and effectively shut down on loss of cold water. The valve shall feature powerful paraffin-based actuation technology and checkstops to prevent cross flow. The valve shall be factory set to 85°F (29°C) with a lockable mean of securing the temperature.

The valve shall be Powers' model ES150 _ _.



A **WATTS** Brand