

Job Name \_\_\_\_\_

Contractor \_\_\_\_\_

Job Location \_\_\_\_\_

Approval \_\_\_\_\_

Engineer \_\_\_\_\_

Contractor's P.O. No. \_\_\_\_\_

Approval \_\_\_\_\_

Representative \_\_\_\_\_

# LEAD FREE\*

## TempTAP™ Gooseneck Thermostatic Faucet



215

### Features

- Eliminates installation of under-the-counter thermostatic valve
- Powers' Advance Thermal Actuator quickly compensates for pressure and temperature fluctuations
- Mixes hot and cold water to deliver tempered water within specified range
- Heavy duty Lead Free\* brass body for durability and to comply with Lead Free\* installation requirements
- Copper supplies feature integrated check valves
- Self-contained cartridge installs in a minute to simplify repairs
- Limits flow to less than 0.5 gpm in the event of cold water failure
- ADA Compliant
- ASSE 1070, IAPMO cUPC listed, and NSF 61 Section 9 Annex G



### Specifications

|  |   |
|--|---|
| Connections .....                          | 3/8" (10 mm) compression inlets with checks     |
| Maximum Operating Pressure .....           | 125 psi (861 kPa)                               |
| Maximum Hot Water Temperature .....        | 194°F (90°C)                                    |
| Minimum Hot Water Supply Temperature ..... | 5°F (3°C) Above Set Point                       |
| Temperature Adjustment Range .....         | 60 – 120°F (15 – 49°C)                          |
| Minimum Flow to ASSE 1070 .....            | 0.5 gpm (1.9 lpm)                               |
| Cold Water Inlet Temperature Range .....   | 39 – 80°F (4 – 27°C)                            |
| Hot Water Inlet Temperature Range .....    | 120 – 180°F (49 – 82°C)                         |
| Factory Set Temperature .....              | 105°F (41°C)                                    |
| Listing .....                              | ASSE 1070, IAPMO cUPC                           |
| Approval Standards .....                   | ASSE 1070, CSA B125.3, NSF 61 Section 9 Annex G |

\*The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.


### Capacity Table\*\*

| Min. Flow to ASSE 1070 | C <sub>v</sub> | 10psi (69 kPa)       | 20psi (138 kPa)      | 30psi (207 kPa)      | 45psi (310 kPa)      | 60psi (414 kPa)      |
|------------------------|----------------|----------------------|----------------------|----------------------|----------------------|----------------------|
| 0.5 gpm<br>1.89 lpm    | 0.345          | 1.08 gpm<br>4.09 lpm | 1.53 gpm<br>5.79 lpm | 1.88 gpm<br>7.12 lpm | 2.30 gpm<br>8.71 lpm | 2.60 gpm<br>9.48 lpm |

\*\*Less Aerator & Outlet temperature 105°F (41°C)

Powers product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Powers Technical Service. Powers reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Powers products previously or subsequently sold.

## Dimensions



## Typical Specification

Faucet shall feature solid Lead Free\* brass cast housing and brass limit stop to prevent over adjustment of handle. Faucet shall be listed to ASSE 1070 and IAPMO cUPC for temperature and pressure protection with a minimum control flow of 0.5 gpm (1.9 lpm). Faucet shall feature a single cartridge design for ease of repair and maintenance and shall provide an approach temperature of no greater than 5°F (3°C). Faucet shall include integral check valves to prevent cross flow and have a metal lever handle in compliance with the American with Disabilities Act (ADA). Faucet shall feature ceramic disc mixing and shall be constructed using Lead Free\* material which shall comply with state codes & standards, where applicable requiring reduced lead content.

Faucet shall be Powers model \_\_\_\_\_.

### NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

## Ordering Information

| Description   | Order Code |
|---|------------|
| <input type="checkbox"/> Gooseneck Spout & 2.0 gpm Aerator  | 205        |
| <input type="checkbox"/> Gooseneck Spout & 2.0 gpm Vandal Resistant Aerator                         | 205VA      |
| <input type="checkbox"/> Gooseneck Spout, 6" Lever Handle & 2.0 Aerator                             | 205-6      |
| <input type="checkbox"/> Gooseneck Spout & 0.5 gpm Outlet   | 205A5      |
| <input type="checkbox"/> Gooseneck Spout & 0.5 gpm Vandal Resistant Outlet                          | 205V5      |
| <input type="checkbox"/> Gooseneck Spout & 1.5 gpm Aerator <sup>+</sup>                             | 205A15     |
| <input type="checkbox"/> Gooseneck Spout & 2.0 gpm Laminar flow outlet                              | 205L       |
| <input type="checkbox"/> Gooseneck Spout & 2.0 gpm Vandal Resistant Laminar flow outlet             | 205VL      |
| <input type="checkbox"/> Gooseneck Spout & 0.5 gpm Laminar flow outlet                              | 205L5      |
| <input type="checkbox"/> Gooseneck Spout & 0.5 gpm Vandal Resistant Laminar flow outlet             | 205VL5     |
| <input type="checkbox"/> Gooseneck Spout, Deck Plate & 2.0 gpm Aerator                              | 215        |
| <input type="checkbox"/> Gooseneck Spout, Deck Plate & 2.0 gpm Vandal Resistant Aerator             | 215VA      |
| <input type="checkbox"/> Gooseneck Spout, Deck Plate, 6" Lever Handle & 2.0 Aerator                 | 0215-6     |
| <input type="checkbox"/> Gooseneck Spout, Deck Plate & 0.5 gpm Outlet                               | 215A5      |
| <input type="checkbox"/> Gooseneck Spout, Deck Plate & 0.5 gpm Vandal Resistant Outlet              | 215V5      |
| <input type="checkbox"/> Gooseneck Spout, Deck Plate & 1.5 gpm Aerator <sup>+</sup>                 | 215A15     |
| <input type="checkbox"/> Gooseneck Spout, Deck Plate & 2.0 gpm Laminar flow outlet                  | 215L       |
| <input type="checkbox"/> Gooseneck Spout, Deck Plate & 2.0 gpm Vandal Resistant Laminar flow outlet | 215VL      |
| <input type="checkbox"/> Gooseneck Spout, Deck Plate & 0.5 gpm Laminar flow outlet                  | 215L5      |
| <input type="checkbox"/> Gooseneck Spout, Deck Plate & 0.5 gpm Vandal Resistant Laminar flow outlet | 215VL5     |

<sup>+</sup>WaterSense® applies to 1.5 gpm aerator models only.

WaterSense® is a registered trademark of the EPA.

# POWERS™

A WATTS Brand

USA: Tel: (800) 669-5430 • Fax: (847) 229-0526 • PowersControls.com

Canada: Tel: (905) 332-4090 • Fax: (905) 332-7068 • PowersControls.ca

Latin America: Tel: (52) 81-1001-8600 • PowersControls.com