Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No.
	Contractor's F.O. No.
Approval	Representative

## LEAD FREE\*

## HydroGuard<sup>®</sup> Master Tempering Valve Supply Fixture

# Series LFLM490 Bottom Inlets/Bottom Outlet — Recessed Cabinet


#### **Features**

- Features Lead Free\* construction to comply with Lead Free\* installation requirements.
- Paraffin-based advanced thermal actuation technology to sense and adjust outlet temperature
- Dirt and lime resistant poppet and seat design
- Virtual shutoff if supply pressure fails
- Stainless steel or white painted cabinets
- Factory tested valve and piping
- Triple-duty checkstops with filters, dial-thermometer, ball valve
- Rough bronze and chrome finishes

#### **Specifications**

### Capacity — Table 1

Flow Capacity When Tested To ASSE 1016 Standard								
	Pressure Differential							
Valve	C <sub>V</sub>	5 psi	10 psi	20 psi	30 psi	45 psi	60 psi	
		(35 kPa)	(69 kPa)	(138 kPa)	(207 kPa)	(310 kPa)	(414 kPa)	
LFLM490	3.42	7.6 gpm	11.0 gpm	15.0 gpm	19.0 gpm	23.0 gpm	27.0 gpm	
		(29 lpm)	(42 lpm)	(57 lpm)	(72 lpm)	(87 lpm)	(102 lpm)	










Advanced Thermal Activation



<sup>\*</sup> The wetted surface of this product contacted by consumable water contains less than one quarter of one percent (0.25%) of lead by weight.

<sup>\*\*</sup> When tested in accordance with ASSE 1017




Note:

Dimensions are shown ±½"

Dimensions in parentheses are in mm

#### **Ordering Information**



#### Typical Specification

Cabinet Supply Fixture (CSF) shall be factory assembled and tested and include a stainless steel or painted steel cabinet. CSF shall feature a HydroGuard® LFLM490 Series Master-Tempering Valve with advanced paraffin-based actuation technology. The valves shall be constructed using Lead Free\* brass. Lead Free\* brass valves shall comply with state codes and standards, where applicable, requiring reduced lead content. CSF shall also include copper piping, ball valve(s) and temperature/pressure gauge for diagnostics. The tempering valve shall have union checkstops, an outlet temperature range of 90 – 160°F (32 – 71°C) (with lockable means), and an approach temperature of 5°F (3°C). Valve shall be ASSE 1017 listed and CSA certified. Minimum flow to ASSE 1017 shall be 0.5 gpm (1.9 lpm).

Valve shall be a Powers model \_\_\_\_\_. All alternatives must have written approval prior to bidding.



A WATTS Brand

**USA:** Tel: (800) 669-5430 • Fax: (847) 229-0526 • PowersControls.com **Canada:** Tel: (905) 332-4090 • Fax: (905) 332-7068 • PowersControls.ca **Latin America:** Tel: (52) 81-1001-8600 • PowersControls.com