Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No.
Approval	Representative

LEAD FREE*

HydroGuard® XP Series LFSH1430 2 Valve Hi/Lo


Supply Fixture Exposed

Features

- Features Lead Free* construction to comply with Lead Free* installation requirements.
- Paraffin-based advanced thermal actuation technology to sense and adjust outlet temperature
- Dirt and lime resistant poppet and seat design
- Virtual shutoff if supply pressure fails
- Vandal-resistant locking mechanism to secure temperature setting
- Factory tested as a complete unit
- Pressure/Temperature Gauge ball valves

Specifications


Connections Maximum Hot Water Supply Temperature Minimum Hot Water Supply Temperature** Minimum Flow*** Maximum Operating Pressure Temperature Adjustment Range**** Let Water left Temperature Range	200°F (93°C) 5°F (3°C) Above Set Point 0.5 gpm (1.9 lpm) 125 psi (861 kPa) 90 – 160°F (32 – 71°C)
Hot Water Inlet Temperature Range	120 – 180°F (49 – 82°C) 40 – 80°F (4 – 27°C)



^{**} With Equal Pressure

Capacity

		Flow	/ Capacity	at 50-50	Mixed Ra	tio		
				Pressure	Drop Acr	oss Valve)	
Model	Min. Flow	Cv	5 psi	10 psi	20 psi	30 psi	45 psi	60 psi
Model	to ASSE 1017	UV	(34 kPa)	(69 kPa)	(138 kPa)	(207 kPa)	(310 kPa)	(414 kPa)
LFSH1432HL	1 gpm	30.0	67 gpm	95 gpm	134 gpm	164 gpm	201 gpm	232 gpm
LF3H143ZHL	4 lpm	30.0	254 lpm	360 lpm	507 lpm	621 lpm	761 lpm	878 lpm
LFSH1434HL	1 gpm	40.4	90 gpm	128 gpm	181 gpm	221 gpm	271 gpm	313 gpm
LF3H1434HL	4 lpm	40.4	341 lpm	485 lpm	685 lpm	837 lpm	1026 lpm	1185 lpm










Advanced Thermal Activation




^{***} Minimum flow when Hi/Lo valve is installed at or near hot water source recirculating tempered water with a properly sized continuously operating recirculating pump.

^{****} Note: Low limit cannot be less than the cold water temperature. For best operation, hot water should be at least 5°F (3°C) above desired set point.

Dimensions





Valve	Inlets	Outlet	PRV	A
LFSH1432HL	1-½"	2"	1-½"	35-¼"
	(40)	(50)	(40)	(685)
LFSH1434HL	2"	2-½"	2"	36-¾"
	(50)	(65)	(50)	(924)

AEM

Note: Dimensions are shown ±½" Dimensions in parentheses are in mm

Ordering Information

<u>Valve</u>	Inlets (in)	Outlet (in)	Order Code
LFMM434/LFSH1432 LFMM434/LFSH1434	1-½" (40mm) 2" (50mm)	2" (50mm) 2-1⁄2" (65mm)	LFSH1432HL LFSH1434HL
<u>Finish</u>			
Rough Bronze			Α
Piping			
Bottom/Top			Е
<u>Cabinets</u>			
Exposed, No Cabinet			M
Alarm+			
None			0
Aqua Sentry®2 for LFSF +Not available with LFS			7

Recirculation Piping Diagram

Please see Piping Diagram Section of this catalog.

Typical Specification

Hi/Lo water temperature control system shall be factory assembled and tested and shall include two thermostatic mixing valves capable of maintaining water temperature to 5° F (3° C) above set point. Hi/Lo shall include HydroGuard® XP LFMM430 and LFSH1430 Series Master-Tempering Valve with advanced, paraffin-based actuation technology. The valves shall be constructed using Lead Free* brass. Lead Free* brass valves shall comply with state codes and standards, where applicable, requiring reduced lead content. Hi/Lo shall also include copper piping, ball valve(s) and temperature/pressure gauge for diagnostics. The tempering valve shall have union checkstops, an outlet temperature range of $90 - 160^{\circ}$ F ($32 - 71^{\circ}$ C) (with lockable means), and a single seat design for positive shutoff. Valve shall be ASSE 1017 listed and CSA certified. Minimum flows to ASSE 1017 shall be 1.0 gpm (4 lpm) for LFSH1432HL and LFSH1434HL.

Valve shall be a Powers' model _____. All alternatives must have written approval prior to bidding.



A WATTS Brand