| Job Name | Contractor |
|--------------|-----------------------|
| Job Location | Approval |
| Engineer | Contractor's P.O. No. |
| | |
| Approval | Representative |

LEAD FREE*

HydroGuard® Master Tempering Valve Supply Fixture

Series LFLM490 Bottom Inlets/Top Outlet — Exposed

Features

- Features Lead Free* construction to comply with Lead Free* installation requirements.
- Paraffin-based advanced thermal actuation technology to sense and adjust outlet temperature
- Dirt and lime resistant poppet and seat design
- Virtual shutoff if supply pressure fails
- · Factory tested valve and piping
- Triple-duty checkstops with filters, dial-thermometer, ball valve
- Rough bronze and chrome finishes

Specifications

Capacity

| Flow Capacity at 50-50 Mixed Ratio | | | | | | | | |
|------------------------------------|------|----------|----------|-----------|-----------|-----------|-----------|--|
| Pressure Differential | | | | | | | | |
| Valve | Cv | 5 psi | 10 psi | 20 psi | 30 psi | 45 psi | 60 psi | |
| | | (35 kPa) | (69 kPa) | (138 kPa) | (207 kPa) | (310 kPa) | (414 kPa) | |
| LFLM490 | 3.42 | 7.6 gpm | 11.0 gpm | 15.0 gpm | 19.0 gpm | 23.0 gpm | 27.0 gpm | |
| | | (29 lpm) | (42 lpm) | (57 lpm) | (72 lpm) | (87 lpm) | (102 lpm) | |







^{*} The wetted surface of this product contacted by consumable water contains less than one quarter of one percent (0.25%) of lead by weight.

^{**} When tested in accordance with ASSE 1017


Dimensions





Note: Dimensions are shown ±½" Dimensions in parentheses are in mm

Ordering Information



Typical Specification

Supply Fixture shall be factory assembled and tested and feature a HydroGuard® LFLM490 Series Master-Tempering Valve with advanced, paraffin-based actuation technology. The valves shall be constructed using Lead Free* brass. Lead Free* brass valves shall comply with state codes and standards, where applicable, requiring reduced lead content. Supply Fixture shall also include copper piping, ball valve(s) and temperature/pressure gauge for diagnostics. The tempering valve shall have union check stops, an outlet temperature range of $90 - 160^{\circ}$ F ($32 - 71^{\circ}$ C) (with lockable means), and an approach temperature of 5° F (3° C). Valve shall be ASSE 1017 listed and CSA certified. Minimum flow to ASSE 1017 shall be 0.5 gpm (1.9 lpm).

Valve shall be a Powers model _____. All alternatives must have written approval prior to bidding.



A WATTS Brand

USA: Tel: (800) 669-5430 • Fax: (847) 229-0526 • PowersControls.com **Canada:** Tel: (905) 332-4090 • Fax: (905) 332-7068 • PowersControls.ca **Latin America:** Tel: (52) 81-1001-8600 • PowersControls.com