| Job Name     | Contractor            |
|--------------|-----------------------|
| Job Location | Approval              |
| Engineer     | Contractor's P.O. No. |
| Approval     | Representative        |

# LEAD FREE\*


# HydroGuard® Master Tempering Valve Supply Fixture

# Series LFLM490 Bottom Inlets/Top Outlet — Wall Mounted Cabinet

### **Features**

- Features Lead Free\* construction to comply with Lead Free\* installation requirements.
- Paraffin-based advanced thermal actuation technology to sense and adjust outlet temperature
- Dirt and lime resistant poppet and seat design
- Virtual shutoff if supply pressure fails
- Stainless steel or white painted cabinets
- · Factory tested valve and piping
- Triple-duty checkstops with filters, dial-thermometer, ball valve
- Rough bronze and chrome finishes


## **Specifications**



<sup>\*\*</sup> When tested in accordance with ASSE 1017

### Capacity

| Flow Capacity at 50-50 Mixed Ratio |      |          |          |           |           |           |           |
|------------------------------------|------|----------|----------|-----------|-----------|-----------|-----------|
| Pressure Differential              |      |          |          |           |           |           |           |
| Valve                              | Cv   | 5 psi    | 10 psi   | 20 psi    | 30 psi    | 45 psi    | 60 psi    |
|                                    |      | (35 kPa) | (69 kPa) | (138 kPa) | (207 kPa) | (310 kPa) | (414 kPa) |
| LFLM490                            | 3.42 | 7.6 gpm  | 11.0 gpm | 15.0 gpm  | 19.0 gpm  | 23.0 gpm  | 27.0 gpm  |
|                                    |      | (29 lpm) | (42 lpm) | (57 lpm)  | (72 lpm)  | (87 lpm)  | (102 lpm) |









Advanced Thermal Activation



# Dimensions 15" (381) 2" (51) (155) (787) 14 3/6" (367)

Note: Dimensions are shown ±½" Dimensions in parentheses are in mm

## Ordering Information


2 5/8

(67)

3 3/8"

(85)

(171)



(51)

(113)

**FINISHED** 

WALL LINE

### **Typical Specification**

Cabinet Supply Fixture (CSF) shall be factory assembled and tested and include a stainless steel or painted steel cabinet. CSF shall feature a HydroGuard® LFLM490 Series Master-Tempering Valve with advanced paraffin-based actuation technology. The valves shall be constructed using Lead Free\* brass. Lead Free\* brass valves shall comply with state codes and standards, where applicable, requiring reduced lead content. CSF shall also include copper piping, ball valve(s) and temperature/ pressure gauge for diagnostics. The tempering valve shall have union checkstops, an outlet temperature range of 90 – 160°F (32 – 71°C) (with lockable means), and an approach temperature of 5°F (3°C). Valve shall be ASSE 1017 listed and CSA certified. Minimum flow to ASSE 1017 shall be 0.5 gpm (1.9 lpm).

Valve shall be a Powers model \_\_\_\_\_. All alternatives must have written approval prior to bidding.



A WATTS Brand

USA: Tel: (800) 669-5430 • Fax: (847) 229-0526 • PowersControls.com

Canada: Tel: (905) 332-4090 • Fax: (905) 332-7068 • PowersControls.ca

Latin America: Tel: (52) 81-1001-8600 • PowersControls.com