




Price List

Commercial Foodservice Plumbing Solutions



- Pre-rinse Units & Components
- Faucets & Accessories
- Specialty Faucets and Sprays
- Pot and Glass Fillers
- Water Stations, Drains & Parts
- Grease Interceptors



Effective March 31, 2025

All prices supersede previous issues, are temporary and subject to change without notice.

Table of Contents

Grease Interceptors	6
WD Series Grease Interceptors	6
GI-K Series High-Capacity Grease Interceptors	6
WD-L Series Low-Profile Grease Interceptors	6
WD-A Semi-Automatic Series Grease Interceptors	6
Grease Interceptor Extensions and Gasket Material	6



Terms and Conditions

TERMS: Net 30 Days. Minimum order \$200 net. Orders below minimum and broken cartons are subject to a \$25.00 handling fee.

1. ACCEPTANCE.

If this writing differs in any way from the terms and conditions of Immediate Buyer's ("Buyer") order or if this writing is construed as an acceptance or as a confirmation acting as an acceptance, then Dormont's ("Seller") acceptance is EXPRESSLY MADE CONDITIONAL ON BUYER'S ASSENT TO ANY TERMS AND CONDITIONS CONTAINED HEREIN THAT ARE DIFFERENT FROM OR ADDITIONAL TO THOSE CONTAINED IN BUYER'S WRITING. Further, this writing shall be deemed notice of objection to such terms and conditions of Buyer. If this writing is construed as the offer, acceptance hereof is EXPRESSLY LIMITED TO THE TERMS AND CONDITIONS CONTAINED HEREIN. In any event, Buyer's acceptance of the goods shall manifest Buyer's assent to Seller's terms and conditions. No addition to or modification of these items will be effective unless set forth in writing and agreed to by Seller.

2. WARRANTIES AND REMEDIES.

a. Warranty.

Seller warrants to Buyer that it holds and will pass marketable title to the goods sold hereunder. Certain of Seller's products come with a Limited Warranty. If Buyer is not the end user of the goods sold hereunder, Buyer agrees to provide to any immediate buyer ("Remote Purchaser") the Limited Warranty and Disclaimer to End-Use (Remote) Purchasers issued by Seller. For the Limited Warranty applicable to Seller's products, please see Seller's published literature that accompanies or relates to those products. Any remedies stated in such warranties are the exclusive and only remedies provided by the Seller for breach of warranty. Certain of Seller's Limited Warranties exclude coverage for any product that is moved to a new location. Seller's products should never be reused.

b. Exclusions and Conditions.

Seller's obligations with respect to the express warranties and remedies contained herein are conditioned on the following: (i) Buyer's return of the nonconforming goods, if authorized by Seller (excluding labor and freight); and (ii) be installed by individuals trained and certified as a professional with respect to such installations, and be installed, used, repaired and maintained by Buyer and Remote Purchaser in accordance with Seller's warnings and instructions, National, State/Province and Local codes or regulations (i.e. National Fuel Code (ANSI Z223.2/NFPA 54); International Fuel Gas Code; Uniform Plumbing Code), standards set by American National Standard Institute, Inc. (ANSI) and/or Canadian Standards Association (CSA) Standards.

3. DISCLAIMER OF IMPLIED WARRANTIES.

SELLER GIVES NO WARRANTIES TO BUYER EXCEPT THOSE EXPRESSLY CONTAINED HEREIN. SELLER DISCLAIMS ALL OTHER WARRANTIES IMPLIED BY LAW, USAGE OF THE TRADE, COURSE OF DEALING OR COURSE OF PERFORMANCE INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE.

4. LIMITATIONS OF LIABILITY.

The following limitations of Seller's liability are acknowledged by the parties to be fair and reasonable and shall apply to any act or omission hereunder, and to any breach of this contract of which these terms and conditions form a part:

a. Disclaimer of Damages.

IN NO EVENT SHALL SELLER BE LIABLE FOR SPECIAL, INDIRECT, CONSEQUENTIAL OR INCIDENTAL DAMAGES WHETHER ARISING UNDER CONTRACT, WARRANTY, TORT, NEGLIGENCE, STRICT LIABILITY OR ANY OTHER THEORY OF LIABILITY. Such damages include but are not limited to loss of profits, loss of use of the goods, damage to property, and claims of third parties.

b. Replacement of Fittings.

Buyer acknowledges that if Seller supplies adapter fittings, and Buyer replaces the adapter fittings supplied by Seller with fittings produced by another manufacturer, then all of Seller's warranties to Buyer and to Remote Purchaser will be voided and Buyer will assume all liability for any damage, injury or loss suffered by Remote Purchaser arising out of this unauthorized modification.

c. Notice and Time of Claims.

(i) Buyer agrees to inspect all products against shipping papers and for damage or shortage upon receipt of goods at destination; and (ii) Every claim for loss, damage in transit, or other cause visible upon inspection shall be made with carrier. Claims for shortage must be made within five (5) days of receipt.

5. TERMS.

Net 30 Days – minimum order of \$200. Interest on accounts overdue more than thirty (30) days will be charged at 2% per month or the highest rate permitted by law, whichever is lower. Orders below minimum and broken cartons are subject to a \$25.00 handling fee. Prices are subject to change. Buyer shall be liable for any collection costs or attorneys' fees incurred as a result of Buyer's failure to pay its account on time.

6. SHIPPING TERMS.

Prepaid and allowed on \$3500 net and over. Under \$3500 net, shipments shall be F.O.B. factory. Buyer is responsible for all freight charges. The above shall apply only to shipments within the continental United States of America unless otherwise indicated by Seller. The method of shipment and carrier shall be selected by Seller.

7. RETURNS.

No returns are to be made to Seller without first obtaining a return authorization number. The return authorization number must be prominently displayed on the return packaging. Absolutely no returns will be accepted or credited without this prior approval. Returns are subject to a 25% restocking charge plus any transportation charges incurred by Seller. Credits will be given only for items that are determined to be eligible for resale by Seller.

8. TAXES.

The Buyer will pay, or reimburse Seller if it pays, any and all taxes or tariffs or any other similar charges imposed upon this contract, the goods covered hereby or the delivery or use or resale thereof.

9. APPLICABLE LAW.

All questions arising hereunder shall be interpreted and resolved in accordance with the Commercial Code of the Commonwealth of Pennsylvania without regard to its conflict of law provisions and excluding the United Nations Convention on the International Sale of Goods.

10. INDEMNIFICATION.

Buyer agrees to indemnify, hold harmless, and defend Seller from and against all claims and lawsuits, including attorney's fees, to the extent that Buyer's negligent acts or omissions to act cause injury, damage or loss to customers of Seller's products.

NOTE: Prices and terms are subject to change without notice and supersede all previous quotations. Seller reserves the right to change or modify product design or construction without prior notice and without incurring any obligation to make such changes and modifications on products previously or subsequently sold. Buyer assumes all responsibility for the final selection, testing and validation of products, including the selection of products for a particular application.

Grease Interceptors

Model #	Ordering Code	Description	List Price (ea/ctn.) USD
WD Series Grease Interceptors			
WD-4	8150959	4 GPM, 8 lb capacity, 2" inlet & outlet, deep seal trap, PDI-certified	\$ 642.14
WD-7	8150960	7 GPM, 14 lb capacity, 2" inlet & outlet, deep seal trap, PDI-certified	\$ 729.47
WD-10	8150961	10 GPM, 20 lb capacity, 2" inlet & outlet, deep seal trap, PDI-certified	\$ 900.46
WD-15	8150962	15 GPM, 30 lb capacity, 2" inlet & outlet, deep seal trap, PDI-certified	\$ 1,044.14
WD-20	8150963	20 GPM, 40 lb capacity, 3" inlet & outlet, deep seal trap, PDI-certified	\$ 1,271.54
WD-25	8150964	25 GPM, 50 lb capacity, 3" inlet & outlet, deep seal trap, PDI-certified	\$ 1,675.37
WD-35	8150965	35 GPM, 70 lb capacity, 3" inlet & outlet, deep seal trap, PDI-certified	\$ 2,181.10
WD-50	8150966	50 GPM, 100 lb capacity, 4" inlet & outlet, deep seal trap, PDI-certified	\$ 2,664.97
GI-K Series High-Capacity Grease Interceptors			
GI-75-K	8142012	75 GPM, 150 lb cap, 4" inlet/outlet, double-wall deep seal trap, integral SS flow	✓ \$ 4,844.24
GI-100-K	8141970	100 GPM, 200 lb cap, 4" inlet/outlet, double-wall deep seal trap, integral SS flow	✓ \$ 7,702.03
GI-150-K	8141976	150 GPM, 300 lb cap, 4" inlet/outlet, double-wall deep seal trap, integral SS flow	✓ \$ 11,620.33
GI-200-K	8141981	200 GPM, 400 lb cap, 4" inlet/outlet, double-wall deep seal trap, integral SS flow	✓ \$ 15,353.11
GI-250-K	8185196	250 GPM, 500 lb cap, 4" inlet/outlet, double-wall deep seal trap, integral SS flow	✓ \$ 19,100.44
GI-300-K	8185587	300 GPM, 600 lb cap, 4" inlet/outlet, double-wall deep seal trap, integral SS flow	✓ \$ 20,966.84
GI-400-K	8186246	400 GPM, 800 lb cap, 4" inlet/outlet, double-wall deep seal trap, integral SS flow	✓ \$ 24,423.09
GI-500-K	8185903	500 GPM, 1000 lb cap, 4" inlet/outlet, double-wall deep seal trap, integral SS flow	✓ \$ 28,381.44
WD-L Series Low-Profile Grease Interceptors			
WD-20-L	8151237	20 GPM, 40 lb capacity, 3" inlet & outlet, deep seal trap, PDI-certified	\$ 2,079.15
WD-35-L	8151746	35 GPM, 70 lb capacity, 4" inlet & outlet, deep seal trap, PDI-certified	\$ 3,422.37
WD-50-L	8100892	50 GPM, 100 lb capacity, 4" inlet & outlet, deep seal trap.	✓ \$ 3,732.77
WD-A Semi-Automatic Series Grease Interceptors			
WD-10-A	8186041	10 GPM, 20 lb cap, 2" inlet/outlet, deep seal trap, internal SS flow, threaded connector	✓ \$ 3,241.63
WD-15-A	8185878	15 GPM, 30 lb cap, 2" inlet/outlet, deep seal trap, internal SS flow, threaded connector	✓ \$ 3,147.03
WD-20-A	8185818	20 GPM, 40 lb cap, 3" inlet/outlet, deep seal trap, internal SS flow, threaded connector	✓ \$ 6,530.52
WD-25-A	8185821	25 GPM, 50 lb cap, 3" inlet/outlet, deep seal trap, internal SS flow, threaded connector	✓ \$ 7,178.12
WD-35-A	8185828	35 GPM, 70 lb cap, 3" inlet/outlet, deep seal trap, internal SS flow, threaded connector	✓ \$ 8,276.85
WD-50-A	8186078	50 GPM, 100 lb cap, 4" inlet/outlet, deep seal trap, internal SS flow, threaded connector	✓ \$ 10,488.88
WD-75-A	8186016	75 GPM, 150 lb cap, 4" inlet/outlet, deep seal trap, internal SS flow, threaded connector	✓ \$ 12,520.78
Grease Interceptor Extensions and Gasket Material			
20WD-12EXT	8151031	12" Extension for WD-20 Grease Interceptor	\$ 1,137.00
25WD-10EXT	8185385	12" Extension for WD-25 Grease Interceptor	\$ 1,443.48
35WD-6EXT	8151041	6" Extension for WD-35 Grease Interceptor	\$ 1,116.21
35WD-12EXT	8151043	12" Extension for WD-35 Grease Interceptor	\$ 1,961.85
50WD-6EXT	8151047	6" Extension for WD-50 Grease Interceptor	\$ 989.45
50WD-10EXT	8185455	10" Extension for WD-50 Grease Interceptor	\$ 1,519.15
50WD-13EXT	8185268	13" Extension for WD-50 Grease Interceptor	\$ 1,574.02
75K-6EXT	8100352	6" Extension for GI-75-K Grease Interceptor	\$ 1,466.18
75K-10EXT	8185456	10" Extension for GI-75-K Grease Interceptor	\$ 1,517.25
100K-10EXT	8185456	10" Extension for GI-100-K Grease Interceptor	\$ 1,517.25
100K-12EXT	8189350	12" Extension for GI-100-K Grease Interceptor	\$ 1,517.11
150K-10EXT	8185456	10" Extension for GI-150-K Grease Interceptor	\$ 1,517.25
WD-GASKET	8188917	25' Roll Gasket Material	\$ 187.29

Note: For optional Threaded Connector (WD, WD-L, Series), add THD to part number. No additional cost.
Additional sizes of grease interceptor extensions available. Also, some Grease Interceptor extensions are Special Order.
(Grease interceptor order value must be \$2,500 or greater to qualify for free shipping. Cannot be combined with other
Dormont products for purposes of qualifying for free shipping)

NOTES



USA: Tel: (800) 367-6668 • Fax: (724) 733-4808 • Foodservice.Watts.com
Latin America: Tel: (52) 55-4122-0138 • Foodservice.Watts.com