
Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No.
Approval	Representative

HydroGuard® XP LFSH1434 Quad Valve Supply Fixture — Wall Mount Cabinet

Features

- Features Lead Free* construction to comply with Lead Free* installation requirements.
- Paraffin-based advanced thermal actuation technology to sense and adjust outlet temperature
- Dirt and lime resistant poppet and seat design
- Virtual shutoff if supply pressure fails
- Vandal-resistant locking mechanism to secure temperature setting
- Factory tested as a complete unit
- Mounted on heavy-duty welded struts
- · Stainless steel or white painted cabinets
- Pressure/Temperature Gauges, Ball valves









Advanced Thermal Activation

Specifications


- * The wetted surface of this product contacted by consumable water contains less than one quarter of one percent (0.25%) of lead by weight.
- ** With Equal Pressure
- *** Minimum flow when Hi/Lo valve is installed at or near hot water source recirculating tempered water with a properly sized continuously operating recirculating pump.
- ***** Note: Low limit cannot be less than the cold water temperature. For best operation, hot water should be at least 5°F (3°C) above desired set point.


Capacity

Flow Capacity at 50-50 Mixed Ratio								
		Pressure Drop Across Valve						
Model	Min. Flow	Cv	5 psi	10 psi	20 psi	30 psi	45 psi	60 psi
	to ASSE 1017		(34 kPa)	(69 kPa)	(138 kPa)	(207 kPa)	(310 kPa)	(414 kPa)
LFSH1434QV	1 gpm	83.3	186 gpm	263 gpm	373 gpm	456 gpm	559 gpm	645 gpm
	4 lpm		704 lpm	996 lpm	1412 lpm	1726 lpm	2116 lpm	2442 lpm



Dimensions





Note: Dimensions are shown ±1/2" Dimensions in parentheses are in mm

Ordering Information

Ordering Information				LFSH1434QVAE
Valve	Inlets	Outlet	Order Code	
Quad Valve	2-1/2" (65mm)	3" (80mm)	QV	
Finish Rough Bronze			А	
Piping Bottom/Top			E	
<u>Cabinets</u>				
Stainless Steel, Wall Mount Q Painted Steel, Wall Mount U				
<u>Alarm</u>				
None			0	

Recirculation Piping Diagram

Please see Piping Diagram Section of this catalog.

Typical Specification

Quad Valve Hi/Lo temperature control system should include four thermostatic valves capable of maintaining water temperature to within the range of 90 - 160°F (32 - 71°C). Valves must compensate for fluctuations due to inlet water temperature changes. The valves shall be constructed using Lead Free* brass. Valves shall comply with state codes and standards, where applicable, requiring reduced lead content. Valves shall have triple-duty checkstops and must have advanced, paraffin-based thermal actuation technology in order to guarantee a precise control when tested in accordance with ASSE 1017 and CSA B125. Thermostatic valves must be ASSE listed and CSA approved. Quad-valve Hi/Lo system must include PRV, ball valves, pressure/temperature gauges and mounted on heavy-duty metal struts. It shall also include a stainless steel or painted steel cabinet. The Hi/Lo system shall be of Powers' Quad Valve Hi/Lo Model ... Any alternate must have a written approval prior to bidding



A WATTS Brand

USA: Tel: (800) 669-5430 • Fax: (847) 229-0526 • PowersControls.com Canada: Tel: (905) 332-4090 • Fax: (905) 332-7068 • PowersControls.ca Latin America: Tel: (52) 81-1001-8600 • PowersControls.com