

# The Quality and Security You Expect from Dormont

# Premium Yellow Coated Stainless Steel Gas Connectors that feature an Antimicrobial Additive to Inhibit the growth of Bacteria, Mold and Mildew

For over 70 years, Dormont<sup>®</sup> has been the leading manufacturer of the highest quality, safe and most durable coated stainless steel gas connectors on the market today.

- With over 180 million safe installations, Dormont gas connectors provide the quality and security you expect for your customers.
  - SafetyShield<sup>®</sup> premium yellow coated gas connectors come in a variety of lengths and diameters for the installer to choose from (see chart on back). Our connectors are compatible with all major brands of gas appliances to ensure that they work to their maximum efficiency.



Dormont.com

#### **High Quality Manufacturing**

SafetyShield gas connectors are produced using proprietary automated manufacturing processes and are 100% leak tested. \_\_\_\_

• CSA design certified\* ANSI Z21.24/CSA 6.10 – Connectors for gas appliances

ANSI Z21.75/CSA 6.27 – Connectors for outdoor appliances and manufactured homes

- No-neck<sup>™</sup> design provides increased flexibility
- Durable, 304 stainless steel construction

### SafetyShield High Performance Yellow Coating

This gas connector features a premium antimicrobial coating to inhibit bacteria growth, improve corrosion and UV protection, and enhance flame and smoke resistance.

- Consistent coverage provides protection along the entire length of the connector.
- Premium antimicrobial coating for increased safety, durability, and longevity
- Limited lifetime warranty for details visit
  www.watts.com/resources/warranty-information
- Provides easy gas line identification

# **Features and Specifications**

- Approved for indoor and outdoor use.
- Temperature rating of connector with adapters: -40°F to 150°F (-40°C to 65.5°C).
- 100% factory leak tested.
- Follow all manufacturers' warnings and instructions.
- Follow local and state codes and The National Fuel Gas Code ANSI Z223.1/NFPA54 (or CAN/CSA B149.1 in Canada).
- When installing a new appliance or when an existing appliance is moved to a new location a NEW gas connector must be used per manufacturer's installation instructions and per product standards ANSI Z21.24/CSA 6.10 and ANSI Z21.75/CSA 6.27.

# **BTU Requirements**

- 1. Check the appliance for the BTU flow capacity required.
- 2. Refer to the chart below to select the connector needed.
- 3. Choose the diameter and length equal to or greater than the BTU requirements of the appliance.

## Natural Gas BTU Chart

Connector Minimum Flow Capacity – <b>For Natural Gas</b> (per ANSI Z21.24/CSA 6.10 & ANSI Z21.75/CSA 6.27) Straight Length Capacity – BTU per Hr 0.64 SG., 1000 BTU per Cu. Ft. at 0.5 inch Water Column (124 Pa) Pressure Drop				
	10C Series	20C Series	30C Series	
Length	OD ¾", ID ¼"	OD 1⁄2", ID 3⁄8"	OD %", ID ½"	
12"	48,000	102,000	180,000	
18"	43,800	93,100	164,200	
24"	40,000	85,000	150,000	
30"	36,400	77,100	136,000	
36"	33,400	71,100	125,000	
48"	28,300	60,500	106,000	
60"	24,900	53,200	93,200	
72"	23,100	49,100	86,000	

# **Propane BTU Chart**

Connector Minimum Flow Capacity – <b>For Propane Gas</b> Straight Length Capacity – BTU per Hr 1.55 SG., 2500 BTU per Cu. Ft. at 0.5 inch Water Column (124 Pa) Pressure Drop				
Length	10C Series 0D %", ID 1⁄4"	20C Series 0D ½", ID ¾"	30C Series 0D 5%", ID 1⁄2"	
12"	76,800	163,200	288,000	
18"	70,080	148,960	262,720	
24"	64,000	136,000	240,000	
30"	58,240	123,360	217,600	
36"	53,440	113,760	200,000	
48"	45,280	96,800	169,600	
60"	39,840	85,120	149,120	
72"	36,960	78,560	137,600	

Dormont product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Dormont Technical Service. Dormont reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Dormont products previously or subsequently sold. Refer to the owner's manual for warranty information.

