Models: 41T, 42T, 44T, 46T

Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No
Approval	Representative

Fabricated Tee Strainers

Models: 41T, 42T, 44T, 46T

Size: 2" - 24"

PRESSURE/TEMPERATURE-NON-SHOCK								
MODEL	RATING							
41T	285psi @ 100°F							
411	150psi @ 565°F							
42T	740psi @ 100°F							
421	300psi @ 838°F							
44T	1480psi @ 100°F							
441	600psi @ 838F							
407	2220psi @ 100°F							
46T	900psi @ 838°F							

Quick opening cover only available for Class 150

41T	Class	150
42T	Class	300
44T	Class	600
46T	Class	900

Typical Service

- Mueller Steam Specialty fabricated strainers are designed to remove foreign particles from pipelines.
- These strainers provide effective and economical protection of pumps, valves, and similar more costly equipment.

Construction

- Standard Class 150, 300, 600 and 900 units available
- Butt-weld or Slip-on Flange connections
- Butt-weld, Weld-neck flange, Ring Joint connections available
- ASME code stamp strainers available

Screens

- Standard material is 304SS.
- Specify other alloy material as required.
- Specify perforation and mesh size for proper particle retention.
- Consider maximum allowable pressure drop when specifying.



Models 41T, 42T, 44T, 46T

General

- See Screen and Basket Options in the mueller Steam Specialty Engineering binder for a partial listing of available options and specification guidelines. "B" signifies a bolted cover; "Q" signifies a quick opening cover.
- Consult factory for specific application information.
- See Specifying Fabricated Strainers page in the Mueller Steam Specialty Engineering binder for guidelines.



The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Mueller Steam Specialty product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Mueller Steam Specialty Technical Service. Mueller Steam Specialty reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Mueller Steam Specialty products previously or subsequently sold.



A WATTS Brand

Dimensions and Weights

5	SIZE	DIMENSIONS									WEIGHT				
		Flar	r nged nd	A We Er	eld	C		E Screen Removal		Hinge Cover		Total			
in.	тт	in.	тт	in.	mm	in.	тт	in.	mm	lbs.	kgs.	lbs.	kgs.		
QUICK OPENING COVER 41T															
6	150	18¼	464	111/4	286	9 ³ /16	219	19	486	7	3.1	108	49		
8	200	22	559	14	356	10%16	292	237/8	606	10	4.5	156	70		
10	250	25	635	17	432	13 ¹ ⁄16	356	295%	752	15	6.8	231	105		
12	300	29	737	20	508	15%16	406	341/8	866	20	9	342	155		
14	350	32	813	22	559	171/8	445	371/8	943	26	11	435	197		
16	400	34	864	24	610	185%	483	405%	1032	30	13	540	245		
18	450	38	965	27	686	211/8	546	46%	1178	42	19	660	300		
20	500	41%	1051	30	762	235%	610	51%	1035	54	24	806	366		
24	600	46	1168	34	864	271/8	699	58%	1483	68	30	1085	493		



Models 41T, 42T, 44T, 46T

S	IZE	DIMENSIONS									WEIGHT			
		A	A _F A _w				C E							
			nged		eld			Screen		Flanged		Weld		
in			nd	End		in		Removal		End		End		
in. BOLTE	mm D COVE	in. D 41 T	тт	in.	тт	in.	тт	in.	тт	lbs.	kgs.	lbs.	kgs.	
2	50	10	254	_	_	53/4	146	111/4	286	30	10	18	8	
21/2	65	111/2	292		_	6 ⁵ / ₈	168	12 ¹⁵ /16	329					
3	80	121/4	311		_	71/16	179	14	356	50	23	30	14	
4	100	141/4	362		_	8 ¹ / ₁₆	205	16½	419	84	38	54	24	
5	125	163/4	425		_	9 ⁵ /16	237	191/2	495	_				
6	150	181/4	464		_	101/8	257	21 ¹ / ₂	546	146	66	96	44	
8	200	22	559	_	_	121/8	308	261/4	667	230	104	152	69	
10	250	25	635	_	_	13 ¹¹ /16	348	301/4	768	352	160	247	112	
12	300	29	737	_	_	15¾	400	35 ³ ⁄16	894	526	239	366	166	
14	350	32	813	_	_	17%	441	387/8	987	220	100	522	237	
16	400	34	864	_	_	187/16	468	41 %	1063	904	410	624	283	
18	450	38	965	_	_	20%16	522	451/8	1165	1078	489	778	353	
20	500	41%	1051	_	_	223/8	568	511/4	1302	1426	647	1066	484	
24	600	46	1168	_	_	247/8	631	571/8	1470	2098	952	1578	716	
BOLTE	D COVE	R 42T				•								
2	50	101/2	268	5	127	61/8	156	113⁄4	298	41	19	23	10	
2 ¹ / ₂	65	12	305	6	152	7	178	137/16	341	—	—	—	_	
3	80	13	330	6¾	171	75⁄8	194	14 ¹¹ / ₁₆	373	82	37	52	24	
4	100	15	381	81⁄4	209	83⁄4	222	17¼	438	125	57	75	34	
5	125	17 ½	445	9¾	248	101//8	257	201/8	511	—	_	—		
6	150	19	483	111⁄4	286	105⁄16	262	221/4	565	231	105	147	67	
8	200	223⁄4	578	14	356	13	330	26 ¹⁵ /16	684	355	161	241	109	
10	250	261/4	667	17	432	15	381	311/2	800	543	246	361	164	
12	300	301/4	768	20	508	171//8	435	361/2	927	825	374	545	247	
14	350	331⁄4	845	22	559	18¾	476	401/8	1019	1102	500	742	337	
16	400	351/2	902	24	610	20	508	433/8	1102	1398	634	898	407	
18	450	39 ½	1003	27	686	221/8	562	483//8	1229	1818	825	1178	534	
20	500	42¾	1085	30	762	231/8	606	525/8	1329	2342	1062	1542	699	
24	600	47 ¹ / ₄	1200	34	864	26%	670	59½	1502	3502	1589	2342	1062	

* Consult factory for dimensions and weights for Class 600, 900, 1500 and 2500 units.

Limited Warranty: Mueller Steam Specialty warrants each product to be free from defects in material and workmanship under normal usage for a period of one year from the date of original shipment. In the event of such defects within the warranty period, the Company will, at its option, replace or recondition the product without charge. This shall constitute the sole and exclusive remedy for breach of warranty, and the Company shall not be responsible for any incidental, special or consequential damages, including without limitation, lost profits or the cost of repairing or replacing other property which is damaged if this product does not work properly, other costs resulting from labor charges, delays, vandalism, negligence, fouling caused by foreign material, damage from adverse water conditions, chemical, or any other circumstances over which the Company has no control. This warranty shall be invalidated by any abuse, misapplication or improper installation of the product. THIS WARRANTY IS IN LIEU OF ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING ANY IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Any implied warranties that are imposed by law are limited in duration to one year.

Some States do not allow limitations on how long an implied warranty lasts, and some States do not allow the exclusion or limitation of incidental or consequential damages. Therefore the above limitations may not apply to you. This Limited Warranty gives you specific legal rights, and you may have other rights that vary from State to State. You should consult applicable state laws to determine your rights.



A WATTS Brand