

Engineering Specification

Job Name _____

Contractor Signature _____

Orion Representative _____

Approval Date _____

Quantity Required _____

Contractor's P.O. No. _____

Please email your completed and signed submittal prior to quote or order entry to oriontanks@wattswater.com.

T9

Point-of-Use Dilution Tank



Specification

Orion T9 POU 5 USG tank shall be cylindrical seamless, stress and defect free, rotationally molded construction including integral cover to uniform wall thickness from virgin PE resins conforming to ASTM D 1248, with **single FIP inlet with dip tube, outlet and vent, plus top 6" cleanout as standard**. All penetrations shall be heat fused to tank wall.

Call customer service if you need assistance with technical details.

Select	Order No.	Description
	735000	One 1.5" FIP Side Inlet, One 1.5" FIP Side Outlet
	735003	One 2" FIP Side Inlet, One 2" FIP Side Outlet

Note: Tanks are made to ± 0.25 in. tolerance.



NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Orion product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Orion Technical Service. Orion reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Orion products previously or subsequently sold.

ORION®

A WATTS Brand

USA: T: (800) 334-6259 • OrionFittings.com

Canada: T: (888) 208-8927 • OrionFittings.ca

Latin America: T: (52) 55-4122-0138 • OrionFittings.com