

Engineering Specification

Job Name _____

Job Location _____

Engineer _____

Approval _____

Contractor _____

Approval _____

Contractor's P.O. No. _____

Representative _____

CO12
PVC/ABS Adjustable Floor
Cleanout w/Round Top
Specification

Watts Light Commercial CO12 PVC or ABS solvent weld adjustable floor cleanout with round nickel bronze, ductile iron, or stainless steel non-skid top, and removable poly cleanout plug.

Call customer service if you need assistance with technical details.


PIPE SIZING	
SUFFIX	DESCRIPTION
-2PVC	2"(51) PVC
-2ABS	2"(51) ABS
-3PVC	3"(76) PVC
-3ABS	3"(76) ABS
-4PVC	4"(102) PVC
-4ABS	4"(102) ABS

OPTIONS	
SUFFIX	DESCRIPTION
-NB	Nickel Bronze Top
-SS	Stainless Steel Top
-DI	Ductile Iron Top
-VP	Vandal Proof Screws

LOAD RATING
MD



CO12-3PVC-DI CO12-3PVC-NB CO12-3PVC-SS



NOTICE

The load classifications are in accordance with the American National Standards ASME A112.21.1M ASME Ratings are as follows:
MD - Safe Live Load 2000-4999 lbs.(900-2250 kg)
The above categories are given as a guide only.
Please consult factory.

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.

