Engineering Specification

Job Name	Contractor	
Job Location	Approval	
Engineer	Contractor's P.O. No.	
Approval	Representative	
	 SKU	

LEAD FREE*

Tankless Water Heater Gas Connection Kit

Kits are designed to simplify the installation, maintenance and operation of tankless water heaters. Kits includes everything you need to connect most tankless water heaters to your gas and water supply.

Features and Specifications

LFTWH Tankless Water Heater Valves:

- 3/4" FPT connection to water lines (75F Model)
- Full port, ¼ turn ball valves with color-coded tee handles and union for fast identification
- Integrated ¼ turn purge and drain valve allows for fast and easy testing and maintenance
- Pressure Relief Valve
- Valve set replaces up to 18 fittings and 16 connections used in typical tankless water heater installations
- Staggered connection points for ease of installation and access
- · No additional adapters required
- NSF / ANSI 61 Certified
- 600 WOG Rated

High BTU Gas Connector:

- CSA Approved for indoor/outdoor use with stationary gas appliances / equipment
- Operating Temperatures with adapters: -40°F to 150°F
- 100% Leak Tested
- Exclusive No-Neck® design increases flexibility
- More corrugations per inch increase flexibility and extend service life
- Use with Natural and LP (propane) gases


Full Port Gas Ball Valve:

- 34" FPT x 34" FPT
- CSA Approved and UL Listed
- Pressure Rating: 125 PSIG
- Temperature Rating: -40°F to 125°F

Materials

LFTWH Tankless Water Heater Valves:

- Body: Lead Free copper silicon alloy body
- Ball: Lead Free brass
- · Seats: PTFE



High BTU Gas Connector:

- Tubing: Annealed, 304 stainless steel (ASTM A240), 1" OD (3/4" ID)
- This gas connector features a premium antimicrobial coating to inhibit bacteria growth, improve corrosion and UV protection, and enhance flame and smoke resistance.
 - Premium antimicrobial coating for increased safety, durability, and longevity
 - Limited lifetime warranty for details visit www.watts.com/resources/warranty-information

Or the Antimicrobial, Hot Dipped Gray PVC Coating.


- Flare Nuts: Carbon steel; zinc trivalent chromate
- Adapters: Carbon steel; zinc trivalent chromate ¾" FIP and ¾" MIP (tapped ½" FIP)

Full Port Gas Ball Valve

- Body: BrassSeats: PTFE
- Ball: Brass (Chrome Plated)

*The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.





NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

A WARNING

Installation and service MUST be performed by qualified installer. Read and follow all Dormont® safety, use, sizing, installation and care instructions and follow all building codes, construction standards, appliance manufacturer recommendations and instructions, and applicable ANSI standards

