

Engineering Specification

Job Name _____
 Orion Representative _____
 Quantity Required _____

Contractor Signature _____
 Approval Date _____
 Contractor's P.O. No. _____

Please email your completed and signed submittal prior to quote or order entry to oriontanks@wattswater.com.

T8

Point-of-Use Dilution Tank



Specification

Orion T8 POU 1.5 USG tank shall be cubic seamless, stress and defect free, rotationally molded construction to uniform wall thickness from virgin PE resins conforming to ASTM D 1248, with **integral cover, with single FIP inlet with dip tube, with single FIP outlet, with 3" top cleanout with cap as standard.** All penetrations shall be heat fused to tank wall.

Call customer service if you need assistance with technical details.

Tank Selection		
Select	Order No.	Description
	734000	One 1.5" FIP Top Inlet, One 1.5" Top Outlet
	734003	One 2" FIP Top Inlet, One 2" FIP Top Outlet
	734001	One 1.5" FIP Top Inlet, One 1.5" FIP Side Outlet
	734002	One 2" FIP Top Inlet, One 2" FIP Side Outlet

Note: Tanks are made to ± 0.25 in. tolerance.



NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Orion product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Orion Technical Service. Orion reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Orion products previously or subsequently sold.

ORION[®]

A WATTS Brand

USA: T: (800) 334-6259 • OrionFittings.com
 Canada: T: (888) 208-8927 • OrionFittings.ca
 Latin America: T: (52) 55-4122-0138 • OrionFittings.com
 ES-OR-T8 2634

